

Hook Spanner With Pin Nose



Material
 Special steel, hardened and blackened.
 Edgewise ground.

489292

Nut Diameter	Thread Size Of Nut DIN 9146 M	Pin Diameter	Pin Depth	Overall Length(mm)	Thickness (mm)	Order Code	Price Each
40 - 42	22 - 24	4	3.5	170	5	137-9027	
45 - 50	26 - 30	5	4	206	6	137-9025	
58 - 62	38 - 42	5	5	240	7	137-9024	
68 - 75	45 - 50	6	5	240	7	137-9022	
80 - 90	52 - 60	6	6	280	8	137-9020	
95 - 100	62 - 70	8	6	280	280	137-9019	
110 - 115	72 - 80	8	8	335	810	137-9017	
120 - 130	85 - 95	8	8	335	10	137-9174	