

**Weller**  
**60 Watt, 120v, 700°F 2-wire Soldering Iron with CT5A7 Tip**



Product Details	
Catalog No.	W60P
UPC Code	037103474087
Type	Temperature Controlled
Wattage	100 W
Temperature Range	600° F/700° F/800° F
Cord Length	6 ft.
Components Supplied	CT5A7
Packaging	Industrial Box/Carton
Tech. Spec.	<a href="#">Solder Safety Warnings.pdf</a>
Lineart	<a href="#">W60P.pdf</a>
Low Res. Image	<a href="#">W60P_100.jpg</a>
High Res. Image	<a href="#">W60P_300.jpg</a>
Stock Item	Normal Stock Item

Package Details (Dimensions)

**Product Features:**

- Uses Weller "closed loop" method of controlling maximum tip temperature
- Portable line voltage iron - no base station required
- Stainless steel modular plug-in heater, greater efficiency & versatility
- Temperature is controlled by tip-600° F, 700° F, and 800° F tips available
- Nominal heat-up time with 700° F tip is 110 seconds
- Two-wire cord set
- Fume extraction adapter kit available - Cat. No. AKFE11
- Uses CT series tips
- Heating element type: Nichrome wound, plug in
- UL and cUL listed