



RJSX03-25L-F



Φ25mm diameter
 Switch Rating:5A/250VAC
 Contact Configuration: 1NO1NC / 2NO1NC
 Operation Type: Momentary / Latching
 The Surface Material: BS/SS/B/BLK
 Dot Illuminated
 IP Degree: IP65



Φ25mm diameter
 Switch Rating:5A/250VAC
 Contact Configuration: 1NO1NC / 2NO2NC
 Operation Type: Momentary / Latching
 The Surface Material: BS/SS/B/BLK
 Ring Illuminated
 IP Degree: IP65



RJSZ05-25L-F-(R/D)-(R/G/Y/O/B/W)-(BS/SS/B/BLK)-(6V/12V/24V/110V/220V)-(IP65)

RJS105 = Single Pole Type 5 Series 1TTL425"?"F qwdrg"Rqrg"V{r g"5"Ugtlku

25 = Diameter (in mm)

L = (Illuminated)

R/D = Ring Illumination / Dot Illumination

R/G/Y/O/B/W = R G Y O B W

BS/SS/B/BLK = Brushed Steel / Shiny Steel / Brass / Black (Surface Finish)

6V/12V/24V/110V/220V = LED Rated Voltage

IP65 = IP Degree, IP 65 Standard

Specification	RJSX03-25L-F-D-X-X-IP65	RJSX03-25L-F-R-X-X-IP65
The Front Shape	Flat Head	Flat Head
Terminal Type	Pin Terminal (2.8x0.5mm)	Pin Terminal (2.8x0.5mm)
Switching	No.2	No.2
Max. Switch Rating	Ith:5A Ui:250VAC	Ith:5A Ui:250VAC
Contact Resistance	≤50mΩ	≤50Mω
Insulation Resistance	≥1000MΩ	≥1000MΩ
Dielectric Intensity	2000VAC	2000VAC
Operating Temp	-20°C ~ +55°C	-20°C ~ +55°C
Mechanical Life	1,000,000cycles	1,000,000cycles
Electrical Life	50,000cycles	50,000cycles
Panel Thickness	1~10mm	1~10mm
Torque	5~14Nm	5~14Nm
Operation Pressure	5.5 ~ 7N	5.5 ~ 7N
Operation Distance	About 2.8mm	About 2.8mm
IP Degree	IP65	IP65
Material	Contact	Silver Alloy
	Button	BS/SS/B/BLK
	Body	BS/SS/B/BLK
	Base	PA
	ROHS	Made to order
LED Spec.	Type	Dot Illuminated (LED)
	Colour	R G Y O B W R G Y O B W
	Rated Voltage	6V/12V/24V/110V/220V
	Life	40,000 hours