

# ScanSnap

Color Image Scanner

## Document Scanners ScanSnap iX500



### ScanSnap iX500



- The scanner that intuitively guides you through every step of the scanning process
- Access your documents anywhere and anytime
  - Scan to and view across a range of popular cloud services
  - Wirelessly scan to your iPad®/ iPhone® and Android™ devices
- A host of automated settings designed for effortless scanning
- Scan your everyday documents from business cards to A4 and even A3
- Scan to: Word, Excel®, E-mail and SharePoint® amongst others

shaping tomorrow with you

FUJITSU

# ScanSnap iX500

Easily digitises various document types




“Total support” from digitisation through to application

## Simple, Speedy & Compact!

### Easily digitises paper based data with the touch of one button

The iX500 facilitates simple PDF generation with the following one touch activated automatic settings and automatic image correction functions:

#### • Blank page detection




#### • Auto deskew and auto orientation



#### • Auto-size detection



#### • Automatic resolution function




#### • Intelligent auto colour detection



## Speedy

Just place a document in the scanner's paper chute, press the “scan” button, and the iX500 starts scanning right away. Furthermore, the iX500 is able to simultaneously scan up to 50 two-sided pages at a speedy 25 pages per minute.

## Scans everything from business cards to A3 sized documents



## ScanSnap Carrier Sheets

Use of a carrier sheet enables iX500 users to digitise larger documents (A3/B4), as well as magazine and newspaper clippings and photographs. Such document containing carrier sheets can be scanned successively or mixed in with regular paper documents.

## Intuitive “Quick Menu” for intelligent and flexible operation

The Quick Menu can be set up to display your ‘Favourite’ scanning destinations or will ‘Recommended’ an application; eg. Scan a business card which will then be automatically recognised and a list of business card related applications will be recommended.

### • Quick Menu for Windows® OS



### • Quick Menu for Mac OS Users



## Create editable Microsoft® Word / Excel® / PowerPoint® files

Top-class OCR engine

**Bundled** **ABBYY FineReader for ScanSnap™ V5.0**

Document received

>> Document scanned

 Now make your paper productive



### ScanSnap Folder, simplifying scanning to your favourite applications

Does your Windows application have an import or browse command? If so you can now easily scan directly to this application even when no scanning interface is available assuming it supports pdf or jpg. Simply browse to the new 'ScanSnap Folder' within your local computer, hit the blue scan button and your document will then be automatically imported into your application and then deleted from 'ScanSnap Folder'. For further information please visit [www.ScanSnapit.com/SSF](http://www.ScanSnapit.com/SSF)

### Generates editable PDF files

- Comes bundled with Adobe® Acrobat® X Standard, which enables users to move beyond merely "seeing" and "printing" generated data, to editing generated PDF files however they like
- Generates password and digital ID attached PDF files that are ideal for safeguarding personal information and other confidential information that needs to be protected

**Bundled** Windows OS only **Perfect for everything from PDF creation to application**  
**ADOBE® ACROBAT® X STANDARD**

### Seamless linking to Cloud services

The iX500 offers direct interaction with your cloud service allowing you to access your documents from any device and at any time or anywhere. The iX500 supports direct scanning to Evernote, Dropbox, Google Docs™, Salesforce and SugarSync.

### Efficiently organises business card information

- Scans large volumes of business cards into digital business card holders
- Enables users to enter scanned data into Excel®, Outlook Express, Salesforce and other databases for future reference

**Bundled** **Business card scanning software**  
**CardMinder™ V5.0**

### Windows OS only ScanSnap iX500 Deluxe includes Rack2-File Smart



Rack2-File Smart allows you to save your scanned and existing digital data in realistic looking bookcases and files that can then be easily retrieved and flipped through the way you may with regular files.

Access and utilise this data anywhere whether through your cloud services or if via a smart device, you can edit, add a comment and then save or redistribute.

Additionally organise / edit image files or scan data imported from ScanSnap in a workspace simulating an actual desktop. You can seamlessly organise your work by categorising data per group and you can also share information with a group with the communication function that links with Facebook.

### Scan via WiFi to your smart devices

The iX500 now offers the unique ability to link directly with your iPad®, iPhone® and Android™ devices via a WiFi connection.



Fitted with a newly developed GI processing engine the iX500 means that users can now wirelessly operate the scanner via their Smart Device and the ScanSnap Connect Application\* creating high quality scanned images that can be saved to the device, manipulated, retrieved at a later date and distributed.

\* ScanSnap Connect Application is available as a free download from the official application distribution service of the device (e.g., Google Play and Apple App Store).

### Enhanced scanning environment centred around a new "GI" image processing engine



The iX500 comes with an inbuilt dual core CPU that takes ScanSnap to that next performance level

- Enables scanning via WiFi to your tablet or mobile device
- Enhanced scanning speeds independent of target device and connectivity
- Offers a paper feeding performance that you would expect with a high speed, high volume device, enhanced through USB 3.0 support

# ScanSnap iX500 Specifications



<b>Product name</b>		<b>ScanSnap iX500</b>
<b>Scanner type</b>		ADF (Automatic Document Feeder), duplex scanning
<b>Scanning modes</b>		Colour, Grayscale, Monochrome, Automatic (Colour / Grayscale / Monochrome detection) <sup>73</sup>
<b>Image sensor / Multi-feed detection</b>		Colour CIS (Contact Image Sensor) x 2 / (front x 1, back x 1) / Supported (Standard) ultrasonic multifeed detection sensor
<b>Light source</b>		3 Colour LED (Red/Green/Blue)
<b>Scanning speed<sup>71</sup></b> (A4 portrait)	Auto Mode <sup>72</sup>	Simplex or Duplex, 25 pages per minute
	Normal mode	Colour & Grayscale 150 dpi, Monochrome 300 dpi, Simplex / Duplex, 25 ppm
	Better mode	Colour & Grayscale 200 dpi, Monochrome 400 dpi, Simplex / Duplex, 25 ppm
	Best mode	Colour & Grayscale 300 dpi, Monochrome 600 dpi, Simplex / Duplex, 25 ppm
	Excellent mode <sup>73</sup>	Colour & Grayscale 600 dpi, Monochrome 1200 dpi, Simplex / Duplex, 7 ppm
<b>Scanning Range</b>	Normal Mode without Carrier Sheet	A4, A5, A6, B5, B6, Business Card, Postcard, Letter, Legal and Custom Size. Max: 216 x 360mm, Min: 50.8 x 50.8mm, Automatically recognizes document size.
	Normal Mode with Carrier Sheet <sup>74</sup>	Use of a carrier sheet permits the scanning of A3, B4, double letter and photographs as well as the document sizes that are listed above
	Long Paper Scanning <sup>74</sup>	863 mm in length
<b>Paper weight (Thickness)</b>		40 to 209 g/m <sup>2</sup> (11 to 56 lb) / A8 size: 127 to 209 g/m <sup>2</sup> or 34 to 56 lb / Cards (ISO7810 ID-1 type conforming) can be used. (thickness 0.76 mm or less) / Embossed card: usable (Landscape only)
<b>Paper chute capacity<sup>75</sup></b>		Maximum 50 sheets (A4 size at 80 g/m <sup>2</sup> )
<b>Interface</b>		USB3.0 (USB2.0 / USB1.1 Supported) <sup>76</sup>
<b>WiFi Interface<sup>77</sup></b>	Observed standards	IEEE802.11b / IEEE802.11g / IEEE802.11n
	Communication mode	Infrastructure mode
	Frequency <sup>78</sup>	2.412 GHz to 2.462 GHz / 2.412 GHz to 2.472 GHz
	Communication distance	Indoors, 50 m (Recommended: indoors, within 25 m) May vary depending on the surrounding environment and the access point to be connected
	Security <sup>79</sup>	WPA-PSK (TKIP / AES), WPA2-PSK (TKIP / AES), WEP (64-bit / 128-bit)
	Easy installation	WPS2.0 supported (button / PIN code)
<b>Power requirement</b>		AC 100 to 240 V, 50 / 60 Hz
<b>Power Consumption</b>	USB connected	During operation: 20 W or less, During sleep mode: 1.6 W or less (WiFi Switch Off)
	WiFi connected	During operation: 20 W or less, During sleep mode: 2.5 W or less
<b>Operation environment</b>		Temperature: 5 to 35 °C (41 to 95 °F) / Relative humidity: 20 to 80 % (Non-condensing)
<b>Dimensions (W x D x H)<sup>16</sup>, Device weight</b>		292 x 159 x 168 mm / 3.0 kg
<b>Environmental compliance</b>		ENERGY STAR <sup>®</sup> / RoHS <sup>11</sup>

- <sup>71</sup> Scanning speeds may vary due to the system environment used.
- <sup>72</sup> Documents measuring approximately 148 mm in length or less are scanned in "Best mode", while other documents are scanned in "Better mode".
- <sup>73</sup> Only computer connection
- <sup>74</sup> ScanSnap iX500 is capable of scanning documents that exceed A4 size in length. It supports the scanning of longer documents in all modes, except for "Excellent mode".
- <sup>75</sup> Maximum capacity varies, depending upon paper weight.
- <sup>76</sup> Some computers may not recognize the ScanSnap when it is connected to a USB 3.0 port. In this case, please use a USB 2.0 port.
- <sup>77</sup> Only Android<sup>™</sup> / iOS in case of WiFi connection.
- <sup>78</sup> Values depends on country.
- <sup>79</sup> IEEE802.1X Authentication is not supported.
- <sup>10</sup> Excluding the stacker and other external attachments.
- <sup>11</sup> PFI LIMITED, a Fujitsu company, has determined that this product meets RoHS requirements (2002/95/EC).

<b>System requirements for Windows</b>		<b>Windows<sup>®</sup> 8 (32-bit / 64-bit)<sup>14</sup></b>	<b>Windows<sup>®</sup> 7 (32-bit / 64-bit)<sup>15</sup></b> <small>*SP1 or later</small>	<b>Windows Vista<sup>®</sup> (32-bit / 64-bit)<sup>16</sup></b> <small>*SP2 or later</small>	<b>Windows<sup>®</sup> XP (32-bit)<sup>17</sup></b> <small>*SP3 or later</small>
<b>Driver / Applications<sup>11,12</sup></b>	ScanSnap Manager V6.0	Supported	Supported	Supported	Supported
	ScanSnap Organizer V5.0	Supported	Supported	Supported	Supported
	CardMinder <sup>™</sup> V5.0	Supported	Supported	Supported	Supported
	ABBYY FineReader for ScanSnap <sup>™</sup> 5.0	Supported	Supported	Supported	Supported
	Scan to Microsoft <sup>®</sup> SharePoint <sup>™</sup> 3.4	Supported	Supported	Supported	Supported
	Adobe <sup>®</sup> Acrobat <sup>®</sup> X Standard <sup>13</sup>	Supported <sup>14</sup>	Supported	Supported	Supported
	Evernote for Win 4.5	Supported	Supported	Supported	Supported

- <sup>11</sup> This product supports Microsoft<sup>®</sup> Windows<sup>®</sup>.
- <sup>12</sup> Please refer to the ScanSnap Web site for latest support information.
- <sup>13</sup> Requires Internet Explorer 7.0 or later; or, Firefox 3.5 or later.
- <sup>14</sup> Please refer to the web site of Adobe Systems Incorporated for latest support information.

<b>System requirements for Mac OS</b>		<b>OS X v10.8</b>	<b>Mac OS X v10.7</b>	<b>Mac OS X v10.6</b>
			<small>(Recommended: 10.7.4 or later)</small>	<small>(Recommended: 10.6.8)</small>
<b>Driver / Applications<sup>11,12</sup></b>	ScanSnap Manager V6.0	Supported	Supported	Supported
	CardMinder <sup>™</sup> V5.0	Supported	Supported	Supported
	ABBYY FineReader for ScanSnap <sup>™</sup> 5.0	Supported	Supported	Supported
	ABBYY FineReader Express Edition for Mac 8.3	Supported	Supported	Supported
	Evernote for Mac 3.3	Supported	Supported	Supported

- <sup>11</sup> This product supports Mac operating systems.
- <sup>12</sup> Please refer to the ScanSnap Web site for latest support information.

<b>Consumables and Options</b>	<b>Part number</b>	<b>Remarks</b>
<b>Consumable kit</b>	PA03656-0001	1 x Pick Roller; 1 x Brake Roller; total maximum lifetime 200,000 documents or 1 year
<b>Cleaning kit</b>	SC-CLE-SS	24 cleaning fluid impregnated wipes
<b>Carrier Sheets</b>	PA03360-0013	5 Carrier Sheets
<b>ScanSnap Bag</b>	PA03951-0651	Intended for ScanSnap iX500, S1500, S1500M, S510, S510M, S500, S500M



<b>Warranty and Service Plans</b>	<b>Remarks</b>
<b>Standard Warranty</b>	2 year Advance Exchange within 1-2 days; Online support; parts, labour and shipping included
<b>Upgrade Options</b>	1-5 year upgrades available on new scanners at time of scanner purchase or within 30 days of purchase, upgrades the warranty
<b>Renewal Options</b>	1-2 year renewals available when warranty or previous service plan has expired

Visit <http://emea.fujitsu.com/assurance> for further information on standard warranty and our Bronze, Silver, Gold and Platinum upgrade options.



"Adobe", "Acrobat" and the Adobe PDF logo are either registered trademarks or trademarks of Adobe Systems Incorporated in the United States and/or other countries.

All names, manufacturer names, brand and product designations are subject to special trademark rights and are manufacturer's trademarks and/or registered brands of their respective owners. All indications are non-binding. Technical data is subject to change without prior notification. Apple, iPad, iPhone, iPod touch and iTunes are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc.

**PFI Imaging Solutions Europe Limited**  
Hayes Park Central  
Hayes End Road, Hayes  
Middlesex UB4 8FE  
England  
Tel: (+44-(0)20) 8573 4444  
Fax: (+44-(0)20) 8573 2643

[www.ScanSnapit.com](http://www.ScanSnapit.com)

**PFI Imaging Solutions GmbH**  
Frankfurter Ring 211  
80807 Munich  
Germany  
Tel: (+49-(0)89) 32378-0  
Fax: (+49-(0)89) 32378-100

**PFI Imaging Solutions S.p.A.**  
Via Nazario Sauro, 38  
20099 Sesto San Giovanni (MI)  
Italy  
Tel: (+39) 0226294.1  
Fax: (+39) 0226294.201

