


G12M-65 Creamback



The G12M Greenback is perhaps the definitive vintage Celestion ceramic magnet guitar speaker. Developed in the mid-sixties, it was quickly adopted by players like Hendrix, Clapton, Beck and Page, who typified the louder and more aggressive blues rock playing styles that came to characterize that era. The G12M-65 Creamback produces the familiar woody G12M tone, but handles greater power making it ideally suited for today's amps, when a vintage tone is desired. The increased power handling brings with it low end grunt complementing the warm and vocal mid range, crunchy upper-mids and sweet, refined highs.

8 Frequency Response



General Specifications

Nominal diameter	12", 305mm
Power rating	65Wrms
Nominal impedance	8
Sensitivity	97dB
Chassis type	Pressed steel
Voice coil diameter	1.75", 44.5mm
Voice coil material	Round copper
Magnet type	Ceramic
Magnet weight	35oz, 0.99kg
Frequency range	75-5000Hz
Resonance frequency, Fs	75Hz
DC resistance, Re	6.7

Mounting Information

Cut-out diameter	11.1", 283mm
Diameter	12.2", 309mm
Magnet structure diameter	5.9", 150mm
Mounting slot dimensions	0.31", 7.9mm Ø
Mounting slot PCD	11.7", 297mm
Number of mounting slots	8
Overall depth	5.1", 130mm
Unit weight	7.9lb, 3.6kg