


**5665/////221**

Minature Paguro gel connector junction box black, 2 cable entry 4.8-6mm with 2 pole terminal block



H=15, L=50, W=18 max

**PRODUCT SPECIFICATIONS**

Minimum cable diameter (mm)	4.8
Maximum cable diameter (mm)	6
Gel material	Sealing bi-component syliconic gel
Fixing system	Screw
Cable entries	2
Number of poles	2
Terminal type	Screw - wp
Body material	Nylon PA66-RV
Colour	Black
Max conductor size (Sq mm)	2.5
Max current (A)	10
Max voltage (V)	250 (Testing now)
Minimum temp rating °C	-30
Max temp rating °C	130
IP rating	68