

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [82-28-5726](#)
Status: **Active**
Description: 1.27mm Pitch Round Conductor Flat Cable - 28 AWG (7 x 36) Stranded Tinned, 26 Circuits, Reel 30.48m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR61126
 UL E61522

General

Product Family Cable
 Series [6800](#)
 Crimp Quality Equipment Yes
 Geographic Area Asia
 Product Name Ribbon
 UPC 800754379359

Physical

Cable Length 30.48m
 Circuits (Loaded) 26
 Insulation PVC
 Net Weight 1704.000/g
 Packaging Type Reel
 Pitch - Termination Interface 1.27mm
 Temperature Range - Operating -20°C to +105°C
 Wire Size AWG 28
 Wire/Cable Type (7x36) Stranded, Tinned

Electrical


Current - Maximum per Contact N/A
 Voltage - Maximum 300V

Material Info

Old Part Number 6800-26-100B

Reference - Drawing Numbers

Sales Drawing SD-6800-001



EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[6800Series](#)

Use With

[70121](#) MX-50™ Slimline Ribbon Cable.
[90584](#) Picoflex® PF-50 IDT Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION