





Standard 215mm Wall Thermometer

215mm plastic wall thermometer with black printed temperature scale on white moulding. Suitable for indoor and outdoor use, this thermometer is ideal for use in the home or the garden.

Product Specifications

- Nominal Range:** -20 to +50°C&F
- Accuracy:** +/- 1.0°C @ ambient
- CE:** N/A
- ROHS/WEEE:** N/A
- Hazard Information (SDS):** See www.brannan.co.uk for information
- Product Material:** Moulding: High Impact Styrene
Glass Tube: Kerosene filled
- Component Weights:** Plastic - 16g
Glass - 6g
- Product Weight:** Unpackaged - 22g
Packaged - 38g
- Product Dimensions :** Unpackaged - 215 x 40 x 8mm
Packaged - 290 x 85 x 9mm
- Display Card Weight:** 10g - 600mu board
- Display Card Dimensions:** 295 x 85 x 0.5mm
- Display PVC Blister Weight:** 6g
- Display PVC Blister Dimensions:** 240 x 62 x 0.5mm



Description	Nominal Range*	Divisions	Barcode	Product No
Standard 215mm	-20 to +50°C	1.0°C	5 011405 147103	14/435/2
Wall Thermometer	-20 to +50°C 0 to +120°F	1.0°C 2.0°F	5 011405 147103	14/435/3

PDS 0010:11:R1

Brannan Thermometers & Instrumentation

Leconfield Industrial Estate • Cleator Moor • Cumbria • CA25 5QE • UK

tel: +44 (0)1946 816600 fax: +44 (0)1946 816625 email: sales@brannan.co.uk web: www.brannan.co.uk

