

AKB-160 - Amplifier Module

100V



PA amplifier module, with 100 V output.

- 1 x 40 WRMS
- Silent operation due to fanless cooling concept
- Balanced line input (XLR) and unbalanced line input (RCA)
- Speaker output via spring-loaded speaker terminals
- Volume control
- Metal housing with mounting brackets



Technical data

Output power	: 40 W _{RMS} , 60 W _{MAX}
Mic input	: -
Aux input	: 390 mV/26 k Ohm, bal.420 mV/11 k Ohm, unbal.
Phono input	: -
Speaker output	: 100 V
Frequency range	: 17-20,000 Hz, -3 dB
Equalizer bass	: -
Equalizer midrange	: -
Equalizer treble	: -
S/N ratio	: > 80 dB
THD	: < 1 %
Power supply	: 230 V~/50 Hz/75 VA
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 213x55x238 mm
Weight	: 3.2 kg
Special feature	: -
Microphone	: -
Aux, phono	: 1 x XLR (line)1 x RCA L/R (line)