

CD-156 - CD Player



Stereo CD and MP3 player, with USB 2.0 interface, for hi-fi and PA applications.

- USB storage media can be connected directly (e.g. USB hard disk, USB flash drive)
- Anti-shock system
- Repeat function (repeat 1, repeat all), random play, standard operating functions
- Adjustable headphone output
- Supplied with infrared remote control with direct track selection
- 482 mm (19") rack installation with supplied mounting brackets, 2 RS
- Audio CD/CD-R/MP3 CD

Technical data

General information

Frequency range	: 20-20,000 Hz
THD	: < 0.1 %
Channel separation	: > 80 dB
Dynamic range	: > 90 dB
S/N ratio	: > 80 dB
Wow and flutter	: not measurable, quartz precision
Output, analogue	: 2 V
Output, digital	: -
Power supply	: 230 V~/50 Hz/25 VA
Admiss. ambient temp.	: 0-40 °C
Dim., player mech.	: 420x90x285 mm, 2 RS(w/o mount. brackets)

Dim., control panel

: -

Weight

: 3.7 kg

Connections

:

Analogue output

: 1 x RCA L/R

Digital output

: -

Fader start

: -

Control connection

: -