


## SA-50 - Amplifier

2 x 25  
W MAX



### Compact universal stereo amplifier

- Silent operation due to fanless cooling concept
- Additional 3.5 mm jack connection with switchable sensitivity at the front panel
- Audio source selector
- Controls for volume, bass and treble
- 6.3 mm headphone output
- Robust metal housing

## Technical data

Max. power	: 2 x 25 W <sub>MAX</sub>
Stereo 4 Ohm	: 2 x 12.5 W <sub>RMS</sub>
Stereo 8 Ohm	: 2 x 10 W <sub>RMS</sub>
Inputs	: PC: 115 mV/12 k Ohm CD: 115 mV/12 k Ohm aux: 115 mV/12 k Ohm player: 115 mV/12 k Ohm (high), 20 mV/32 k Ohm (low)
Frequency range	: 20-20,000 Hz
S/N ratio	: > 65 dB
Digital echo	: -
Equalizer	: bass: ±12 dB treble: ±12 dB
Power supply	: 230 V~/50 Hz/50 VA
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 212x56x200 mm
Weight	: 1.9 kg
<b>Connections</b>	: PC: RCA L/R CD: RCA L/R aux: RCA L/R player: 3.5 mm jack speaker: spring-load. speaker term.