



Main

Commercial Status	Commercialised
Range	ClimaSys CC
Category	Electronic hygrostat
Product compatibility	Resistance heater Fan
Humidity setting range	20...80 %
Display type	LCD screen
Information displayed	Relative humidity

Complementary

Input voltage	110...240 V AC
Maximum switching capacity	5 A 30 V DC 8 A 250 V AC
Electrical connection	4 terminals 2.5 mm ²
Mounting mode	By screws Clipped
Height	External: 85 mm
Width	External: 56 mm
Depth	External: 44 mm
Mounting location	On mounting plate 35 mm DIN rail Spacial upright Cross rails
Hysteresis	3 %
Number of outputs	2 output(s)ventilation/heating function
Material	PC
Colour	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UL UR

RoHS compliance

RoHS EUR status	Compliant
RoHS EUR conformity date(Y Y W W)	0940

Contractual warranty

Period	18 months
--------	-----------