

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19069-0217](#)  
**Status:** **Active**  
**Overview:** Ring Tongue - Spade Terminals  
**Description:** Krimptite™ Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 24.18mm

**Documents:**

[Drawing \(PDF\)](#)      [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA      LR18689  
 UL      E32244

**General**

Product Family      Ring and Spade Terminals  
 Series      [19069](#)  
 Crimp Quality Equipment      Yes  
 Mil-Spec      N/A  
 Overview      [Ring Tongue - Spade Terminals](#)  
 Product Name      Krimptite™  
 Type      Ring  
 UPC      800755067309

**Physical**


Barrel Type      Closed  
 Insulation      None  
 Material - Plating Mating      Tin  
 Material - Plating Termination      Tin  
 Net Weight      2.177/g  
 Packaging Type      Bag  
 Plating min - Mating      2.540µm  
 Plating min - Termination      2.540µm  
 Stud Size      10 (M5)  
 Termination Interface: Style      Crimp or Compression  
 Wire Size AWG      10, 12  
 Wire Size mm²      4.00 - 6.00

**Material Info**

Old Part Number      C-130-10

**Reference - Drawing Numbers**

Product Specification      PS-19902-011, PS-19902-013  
 Sales Drawing      CCD10101



*image - Reference only*

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

**Contains SVHC: No  
Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[19069Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade™ Hand Crimp Tool	<a href="#">0640030100</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640070100</a>

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**