



Heavy Duty Steel Knockdown 4-Post Open Frame

Rack *DC4R Series*

Adjustable Depth



The all new Hammond DC4R Open Rack series is one of the most economical solutions to house IT equipment in wiring closets or data centers. In situations where the wiring closet itself is under lock and key and accessed by a limited number of people, full cabinets having locking doors and side panels may not be required resulting in a significant cost savings.

Standard Features

- Available in 24U and 44U and in two convenient adjusting depths.
 - 24"-36" for standard rackmount equipment.
 - 32"-48" for extra deep equipment.
- Includes two (2) pairs of 19" mounting EIA-310-D compliant square-hole rails.
 - Optional pair of rails available for multiple mounting depths.
- Mounting rails include permanent rack unit space indicators.
- Rail depth L-bracket restrict the installer from over-extending the rack. This ensures the integrity of the rack.
- Includes one (1) set of two (2) horizontal cable manager bars. Additional cable manager bars available by ordering part number DC4RSHCM.
- Finished in smooth black powder paint.

Specifications

- Constructed of 12-gauge steel.
- Suggested load capacity of 2,000 lb.
- RoHS Compliant.
- Manufactured in North America.

Updates

- **01-Jun-2013:** The DC4R Series has been completely redesigned to ease in assembly and overall use. With the reduction in the amount of hardware and self-squaring design, the DC4R takes just minutes to assemble. With the new infinitely adjustable depth rail system, the overall depth can be adjusted without removing the installed equipment.

Accessories

[Two Post Mounting Cantilever Shelf](#)

[Two Post Mounting Adjustable Shelf](#)

[Two Post Mounting Keyboard & Monitor Shelf](#)

[Two Post Mounting Deep Channel](#)

[Two Post Centered Shelf](#)

[Two Post Mounting Clamping Shelf](#)

[Two Post Mounting Deep Channel Battery Shelf](#)

[Two Post Mounting Adjustable Depth](#)

[Shelf](#)
[Four Post Mounting Adjustable Depth Shelf](#)
[Four Post Mounting Sliding Shelf](#)
[Hinged Acrylic Door Panel Cover](#)
[Outlet Strips](#)
[Rack Panels](#)
[Rack Unit Label](#)

[Rack and Cabinet](#)
[Baying/Ganging/Joining Kit](#)

[DIN Rail](#)
[Two or Four Post Mounting Storage Drawer](#)
[Four Post Mounting Keyboard Drawer](#)
[Cable Management](#)
[Mounting Hardware](#)
[Grounding](#)
[Light Duty Caster Set for Open Frame Rack](#)

Part No.	Overall Dimensions (with base facing outwards)				Mounting Dimensions				
	Height	Width	Min Depth	Max Depth	Height	Width	Rack Units	Min Depth	Max Depth
DC4R24	48.12	20.50	36.00	48.00	42.00	19.00	24U	24.00	36.00
DC4R2448	48.12	20.50	44.00	60.00	42.00	19.00	24U	32.00	48.00
DC4R44	83.13	20.50	36.00	48.00	77.00	19.00	44U	24.00	36.00
DC4R4448	83.13	20.50	44.00	60.00	77.00	19.00	44U	32.00	48.00

DC4R Specific Accessories

Part No.	Description
DC4RSHCM	Additional Horizontal Cable Bars (2)
DC4RPR24	Additional pair of rails for DC4R 24U
DC4RPR44	Additional pair of rails for DC4R 44U

Data subject to change without notice.