

BMP®41 General Identification Material:

Indoor / Outdoor Grade Facility & Safety Labels

This low-shrink, continuous vinyl material works for a variety of applications, including 5S labels, pipe markers, chemical labels and more. Lasting up to 8-10 years outdoors, these labels offer excellent resistance to oils, detergents, dirt, grime and many solvents.

- **B-595 Indoor/Outdoor Vinyl Material** - Permanent adhesive, very pliable, good for rough surfaces and outdoor use, wide range of colors. Temp. Range: -40°F to 248°F (-40°C to 120°C). UL recognized.



Figure 33



| Diagram | Catalog # | B# | Material | Color | Label Width A Inch (mm) | Label Height B Inch (mm) | Labels/Roll |
|--|--------------------|-------|----------|----------|----------------------------|-----------------------------|----------------|
| B-595 – Indoor/Outdoor Vinyl Tape | | | | | | | |
| Fig. 33 | MC-500-595-WT-BK | B-595 | Vinyl | BK on WT | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-WT-BK | B-595 | Vinyl | BK on WT | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-WT-BK | B-595 | Vinyl | BK on WT | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-YL-BK | B-595 | Vinyl | BK on YL | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-YL-BK | B-595 | Vinyl | BK on YL | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-YL-BK | B-595 | Vinyl | BK on YL | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-OR-BK | B-595 | Vinyl | BK on OR | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-OR-BK | B-595 | Vinyl | BK on OR | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-OR-BK | B-595 | Vinyl | BK on OR | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-BL-WT | B-595 | Vinyl | WT on BL | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-BL-WT | B-595 | Vinyl | WT on BL | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-BL-WT | B-595 | Vinyl | WT on BL | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-RD-WT | B-595 | Vinyl | WT on RD | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-RD-WT | B-595 | Vinyl | WT on RD | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-RD-WT | B-595 | Vinyl | WT on RD | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-GN-WT | B-595 | Vinyl | WT on GN | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-GN-WT | B-595 | Vinyl | WT on GN | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-GN-WT | B-595 | Vinyl | WT on GN | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-WT-RD | B-595 | Vinyl | RD on WT | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-WT-RD | B-595 | Vinyl | RD on WT | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-WT-RD | B-595 | Vinyl | RD on WT | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-BK-WT | B-595 | Vinyl | WT on BK | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-BK-WT | B-595 | Vinyl | WT on BK | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-BK-WT | B-595 | Vinyl | WT on BK | 1.000 (25.4) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-CL-BK | B-595 | Vinyl | BK on CL | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-CL-BK | B-595 | Vinyl | BK on CL | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-CL-BK | B-595 | Vinyl | BK on CL | 1.000 (25.4) | 20 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-500-595-CL-WT | B-595 | Vinyl | WT on CL | 0.500 (12.7) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC-750-595-CL-WT | B-595 | Vinyl | WT on CL | 0.750 (19.1) | 25 ft. (7.6 m) | 1 roll (cont.) |
| Fig. 33 | MC1-1000-595-CL-WT | B-595 | Vinyl | WT on CL | 1.000 (25.4) | 20 ft. (7.6 m) | 1 roll (cont.) |

Get the job done for less with a Brady Starter Kit.



BMP41 Starter Kits

| Catalog # | Description |
|--------------|-------------------------------|
| BMP41-KIT-VD | BMP41 DataComm Starter Kit |
| BMP41-KIT-EL | BMP41 Electrical Starter Kit |
| BMP41-KIT-GI | BMP41 Facility ID Starter Kit |

*Printer ships with BMP41 Rechargeable Battery Pack, MC1-1000-595-WT-BK cartridge, USB Cable, AC Adapter, Product CD, Brady Printer Drivers CD and Quick Start Guide.

BMP41 DataComm Starter Kit Includes:

- 1 - BMP41 Label Maker Standard Package (BMP41-KIT)
- 1 - BMP41 Hard Case (BMP41-HC)
- 1 - B-427 1.0" White Label Roll (M-51-427)
- 1 - B-412 0.475" White Label Roll (MC-475-412)
- 1 - B-5951.0" Black on Yellow Label Roll (MC1-1000-595-YL-BK)
- 1 - B-5951.0" Black on White Label Roll (MC1-1000-595-WT-BK)

BMP41 Electrical Starter Kit Includes:

- 1 - BMP41 Label Maker Standard Package (BMP41-KIT)
- 1 - BMP41 Hard Case (BMP41-HC)
- 1 - B-427 1.0" White Label Roll (M-143-427)
- 1 - B-498 1.0" White Label Roll (M-48-498)
- 1 - B-342 0.75" White Label Roll (M-187-075-342)
- 1 - B-595 1.0" Black on Orange Label Roll (MC1-1000-595-OR-BK)
- 1 - B-595 1.0" Black on White Label Roll (MC1-1000-595-WT-BK)

BMP41 Facility ID Starter Kit Includes:

- 1 - BMP41 Label Maker Standard Package (BMP41-KIT)
- 1 - B-595 1.0" Black on Yellow Label Roll (MC1-1000-595-YL-BK)
- 1 - B-595 1.0" Red on White Label Roll (MC1-1000-595-WT-RD)
- 1 - B-595 1.0" White on Green Label Roll (MC1-1000-595-GN-WT)
- 1 - B-595 1.0" Black on White Label Roll (MC1-1000-595-WT-BK)
- 1 - B-483 1.0" White Label Roll (M-60-483)