

700F Series

Tubeaxial

70x70x15mm



- DC fans with electronically commutated external rotor motor. Fully integrated commutation electronics.

- With electronic protection against reverse polarity. The fan only operates when the polarity is correct. Impedance-protected against blocking and overloading.

- Mounting from either face using four 4.3 mm holes.

- Fan of fiberglass reinforced plastic. PBTP housing, PA impeller.

- Air exhaust over struts. Rotational direction CCW looking at rotor.

- Electrical connection via 2 leads AWG 28, TR 64. Stripped and tinned ends.

- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	CFM @ 0	Curve	Volts	Voltage Range	Power (W)	dBA	Max Ambient Temp C	Wgt. (lbs)	Type Of Bearing	Features
712FL	16.2	1	12	8 to 13.8	0.6	25	70	0.19	Sintec	Leads
712FM	21.2	2	12	8 to 13.8	1.1	32	70	0.19	Sintec	Leads
712F	25.9	3	12	8 to 13.8	1.7	36	70	0.19	Sintec	Leads
714F	25.9	3	24	12 to 30	1.7	36	70	0.19	Sintec	Leads

Tacho signal /2 and /12 available on request.
Alarm signal /37 and /39 available on request.

