



# Catamount®

**Grommeting**

**T&B Catalog Number:**

GRPE-100-9-C

**UPC Number:**

72849411754

**Status:**

Active


**Description:**

Extruded Grommeting Natural Polyethylene For Max. Panel Thickness .100, 100 Feet Per Roll

## Features

Used to line panel edges and knockouts where the chafing of wires is a concern.

Available in 8 stock sizes in 100-ft. lengths for panels from .040 - .250 inches thick and in a variety of stocked materials to cover a wide range of applications.



## General

Style	Extruded
Material	Polyethylene
Color	Natural

## Dimension Information

For Panel Thickness Max (inches)	0.100
C (inches)	0.045
D (inches)	0.220
E (inches)	0.210

## Specifications

Flammability Rating	UL 94 HB
---------------------	----------

## Tooling

Application Tools	SR-100
-------------------	--------

## Packaging

T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	10
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	1.02 lbs. Each

## Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com