



Sta-Kon®

Disconnects

T&B Catalog Number:

RA18D

UPC Number:

78621080398

Status:

Active

Description:

Insulated Nylon Wristlock Disconnects For Wire Range 22-18 Length 0.99, Red

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

General

Disconnect Type	Wristlock
Insulation Type	Insulated Nylon
Terminal Series	RA
Material	Brass
Finish	Electro -Tin Plated
Color	Red
Wire Range	22-18

Dimension Information

Maximum Insulation (inches)	.136
Stock Thickness	.03
A (inches)	.99

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Recommended Tool	WT2000

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.35 lbs. per 100
Alternate Package Qty	RA23

Application Support


Wire Guide Tables	Available on Website
-------------------	----------------------

Notes

Picture shows wristlock assembled as 2 pieces. Parts are sold by the piece, not assemblies.

Certifications

RoHS Compliance	Yes
-----------------	-----



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com