


Cable Ties and Accessories

3M™ Cable Ties are designed to secure wire bundles and harness components quickly, without slipping. Featuring a self-locking head and a locking mechanism, they are designed to handle temperatures up to 185°F (85°C). Available in several strengths and lengths, including screw mount. Most are plenum rated and USA made.



Cable Ties Part Number Naming Convention

The product name has been changed to better identify the characteristics of each tie.

CT D C T X - P

Example:
Catalog Number: CT4BK18-C

CT	D	C	T	X	-	P
CT = Cable Ties CTB = Mounting Bases	D = Dimensions (inches) Ties = Length Bases = Length X Width	C = Color BK = Black NT = Natural RD = Red BG = Beige	T* = Tensile (pounds) 18 = Miniature 40 = Intermediate 50 = Standard 120 = Light Heavy Duty 175 = Heavy Duty	X = Special Features _ = Standard Tie (Blank) S = Screw Mount A = Adhesive Mount	-	P = Package Size (Roman Numeral) M = 1,000 D = 500 C = 100 L = 50

*Cable Tie Base Part Numbers do not include Tensile.

Section

Page


3M™ Cable Ties	109-115
3M™ Miniature Cable Ties (18 lb, 8 kg)	109
3M™ Intermediate Cable Ties (40 lb, 18 kg)	110
3M™ Standard Cable Ties (50 lb, 23 kg).....	111
3M™ Light Heavy Duty Cable Ties (120 lb, 54 kg).....	112
3M™ Heavy Duty Cable Ties (175 lb, 79 kg)	113
3M™ Screw Mount Ties (Standard #10 Stud)	114
3M™ Cable Ties - Cable Tie Assortment Packs	115
3M™ Cable Bases and Stackers	115-116
3M™ Cable Stackers.....	115
3M™ Cable Tie Mounting Bases	116
3M™ Hook and Loop Fasteners	117-118
3M™ Hook and Loop Fasteners.....	117
3M™ Scotchmate™ Reclosable Fasteners.....	118
3M™ Dual Lock™ Fasteners	119-120
3M™ Dual Lock™ Fasteners	119
3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	120


3M™ Cable Ties


3M™ Miniature Cable Ties (18 lb, 8 kg)

3M™ Miniature Cable Ties are small lightweight cable ties for use in holding applications up to 18 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength 18 lb (8 kg)
 Max. Temperature Use 185°F (85°C)
 RoHS 2011/65/EU Yes

Agency Approvals 

Country of Origin 



Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Min. Bundle Dia.	Max. Bundle Dia.	Items per Bag	Items per Case
CT4BK18-C	051128-59273	Black	Yes	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.062" (1,6 mm)	0.75" (19,1 mm)	100	1000
CT4BK18-M	051128-59274	Black	Yes	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.062" (1,6 mm)	0.75" (19,1 mm)	1000	10,000
CT4NT18-C	051128-59275	Natural	No	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.062" (1,6 mm)	0.75" (19,1 mm)	100	1000
CT4NT18-M	051128-59276	Natural	No	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.062" (1,6 mm)	0.75" (19,1 mm)	1000	10,000
CT6BK18-C	051128-59277	Black	Yes	6.10" (155 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.25" (31,8 mm)	100	1000
CT6NT18-C	051128-59278	Natural	No	6.10" (155 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.25" (31,8 mm)	100	1000
CT6NT18-M	051128-59279	Natural	No	6.10" (155 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.25" (31,8 mm)	1000	10,000
CT8BK18-C	051128-59280	Black	Yes	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	100	1000
CT8BK18-M	051128-59281	Black	Yes	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	1000	10,000
CT8NT18-C	051128-59282	Natural	No	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	100	1000
CT8NT18-M	051128-59283	Natural	No	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	1000	10,000

3M™ Cable Ties

3M™ Intermediate Cable Ties (40 lb, 18 kg)


3M™ Intermediate Cable Ties are a great solution for holding applications up to 40 lb. They provide an economical alternative to standard cable ties when higher tensile strength is not required. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength 40 lb (18 kg)
 Max. Temperature Use 185°F (85°C)
 RoHS 2011/65/EU Yes

Agency Approvals



Country of Origin




Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Min. Bundle Dia.	Max. Bundle Dia.	Items per Bag	Items per Case
CT6BK40-C	051128-59284	Black	Yes	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.25" (31,8 mm)	100	1000
CT6BK40-M	051128-59285	Black	Yes	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.25" (31,8 mm)	1000	10,000
CT6NT40-C	051128-59286	Natural	No	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.25" (31,8 mm)	100	1000
CT6NT40-M	051128-59287	Natural	No	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.25" (31,8 mm)	1000	10,000
CT8BK40-C	051128-59288	Black	Yes	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	100	1000
CT8BK40-M	051128-59289	Black	Yes	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	1000	10,000
CT8NT40-C	051128-59290	Natural	No	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	100	1000
CT8NT40-M	051128-59291	Natural	No	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	1000	10,000


3M™ Cable Ties


3M™ Standard Cable Ties (50 lb, 23 kg)

3M™ Standard Cable Ties are the most common sized ties and provide a standard level of performance for general-use holding applications up to 50 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength 50 lb (23 kg)
 Max. Temperature Use 185°F (85°C)
 RoHS 2011/65/EU Yes

Agency Approvals 

Country of Origin 



Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Min. Bundle Dia.	Max. Bundle Dia.	Items per Bag	Items per Case
CT8BK50-C	051128-59293	Black	Yes	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.87" (47,5 mm)	100	1000
CT8BK50-M	051128-59294	Black	Yes	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.87" (47,5 mm)	1000	10,000
CT8NT50-C	051128-59297	Natural	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.87" (47,5 mm)	100	1000
CT8NT50-M	051128-59299	Natural	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	1.87" (47,5 mm)	1000	10,000
CT8RD50-C	051128-59559	Red	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	2.00" (50,8 mm)	100	1000
CT11BK50-C	051128-59300	Black	Yes	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	3.00" (76,2 mm)	100	1000
CT11BK50-D	051128-59301	Black	Yes	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	3.00" (76,2 mm)	500	5000
CT11NT50-C	051128-59302	Natural	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	3.00" (76,2 mm)	100	1000
CT11NT50-D	051128-59303	Natural	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	3.00" (76,2 mm)	500	5000
CT11RD50-C	051128-59560	Red	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	3.00" (76,2 mm)	100	1000
CT15BK50-C	051128-59304	Black	Yes	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	4.00" (101,6 mm)	100	500
CT15BK50-D	051128-59305	Black	Yes	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	4.00" (101,6 mm)	500	2500
CT15NT50-C	051128-59307	Natural	No	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	4.00" (101,6 mm)	100	500
CT15NT50-D	051128-59309	Natural	No	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	0.062" (1,6 mm)	4.00" (101,6 mm)	500	2500

3M™ Cable Ties

3M™ Light Heavy Duty Cable Ties (120 lb, 54 kg)

3M™ Light Heavy Duty Cable Ties are commonly used in more demanding commercial and industrial jobs when extra strength is required to hold up to 120 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength 120 lb (54 kg)
Max. Temperature Use 185°F (85°C)
RoHS 2011/65/EU Yes

Agency Approvals



Country of Origin




Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Min. Bundle Dia.	Max. Bundle Dia.	Items per	Items per Case
CT8BK120-L	051128-59310	Black	Yes	9.00" (229 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	0.19" (4,8 mm)	2.00" (50,8 mm)	50	500
CT8NT120-L	051128-59311	Natural	No	9.00" (229 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	0.19" (4,8 mm)	2.00" (50,8 mm)	50	500
CT15BK120-C	051128-59312	Black	Yes	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	0.19" (4,8 mm)	4.00" (101,6 mm)	100	500
CT15BK120-D	051128-59313	Black	Yes	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	0.19" (4,8 mm)	4.00" (101,6 mm)	500	2500
CT15NT120-C	051128-59315	Natural	No	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	0.19" (4,8 mm)	4.00" (101,6 mm)	100	500
CT15NT120-D	051128-59317	Natural	No	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	0.19" (4,8 mm)	4.00" (101,6 mm)	500	2500

3M™ Cable Ties

3M™ Heavy Duty Cable Ties (175 lb, 79 kg)

3M™ Heavy Duty Cable Ties provide an added level of strength plus a larger bundle diameter for heavy duty jobs up to 175 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

The 36" and 48" ties are also suitable for use with UL non-metallic air ducts and air connectors.



Tensile Strength 175 lb (79 kg)
Max. Temperature Use 185°F (85°C)
RoHS 2011/65/EU Yes
Agency Approvals



	CT24BK175-L	CT24NT175-L	CT36BK175-L
UPC	051128-59318	051128-59319	051128-59320
Color	Black	Natural	Black
UV Resistance	Yes	No	Yes
Length	24.00" (610 mm)	24.00" (610 mm)	36.00" (914 mm)
Width	0.34" (8,6 mm)	0.34" (8,6 mm)	0.34" (8,6 mm)
Thickness	0.09" (2,3 mm)	0.09" (2,3 mm)	0.09" (2,3 mm)
Min. Bundle Dia.	0.19" (4,8 mm)	0.19" (4,8 mm)	0.19" (4,8 mm)
Max. Bundle Dia.	7.20" (183 mm)	7.20" (183 mm)	11.00" (279 mm)
Items per Bag	50	50	50
Items per Case	500	500	500
Country of Origin			
	CT36NT175-L	CT48BK175-L	CT48NT175-L
UPC	051128-59321	051128-59322	051128-59323
Color	Natural	Black	Natural
UV Resistance	No	Yes	No
Length	36.00" (914 mm)	47.90" (1217 mm)	47.90" (1217 mm)
Width	0.34" (8,6 mm)	0.36" (9,1 mm)	0.36" (9,1 mm)
Thickness	0.09" (2,3 mm)	0.07" (1,8 mm)	0.07" (1,8 mm)
Min. Bundle Dia.	0.19" (4,8 mm)	1.5" (38 mm)	1.5" (38 mm)
Max. Bundle Dia.	11.00" (279 mm)	14.60" (372 mm)	14.60" (372 mm)
Items per Bag	50	50	50
Items per Case	500	500	500
Country of Origin		-	-

3M™ Cable Ties

3M™ Screw Mount Ties (Standard #10 Stud)

3M™ Screw Mount Cable Ties allow precise and controlled positioning of standard and heavy duty cables up to 120 lb. The easy-to-use ties can be quickly mounted to walls and structures with screws, bolts or rivets for added security. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.



Stud Size 10

Max. Temperature Use 185°F (85°C)

RoHS 2011/65/EU Yes

Agency Approvals



Country of Origin




	CT8BK50S-C	CT8BK50S-M	CT8NT50S-C	CT8NT50S-M
UPC	051128-59292	051128-59295	051128-59296	051128-59298
Color	Black	Black	Natural	Natural
UV Resistance	Yes	Yes	No	No
Length	8.60" (218 mm)	8.60" (218 mm)	8.60" (218 mm)	8.60" (218 mm)
Width	0.18" (4,6 mm)	0.18" (4,6 mm)	0.18" (4,6 mm)	0.18" (4,6 mm)
Thickness	0.06" (1,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)
Tensile Strength	50 lb (23 kg)	50 lb (23 kg)	50 lb (23 kg)	50 lb (23 kg)
Min. Bundle Dia.	0.062" (1,6 mm)	0.062" (1,6 mm)	0.062" (1,6 mm)	0.062" (1,6 mm)
Max. Bundle Dia.	2.00" (50,8 mm)	2.00" (50,8 mm)	2.00" (50,8 mm)	2.00" (50,8 mm)
Items/ Bag	100	1000	100	1000
Items/ Case	1000	10,000	1000	10,000
	CT15NT50S-L	CT15NT50S-D	CT15NT120S-L	CT15NT120S-D
UPC	051128-59306	051128-59308	051128-59314	051128-59316
Color	Natural	Natural	Natural	Natural
UV Resistance	No	No	No	No
Length	15.10" (384 mm)	15.10" (384 mm)	15.70" (399 mm)	15.70" (399 mm)
Width	0.18" (4,6 mm)	0.18" (4,6 mm)	0.30" (7,6 mm)	0.30" (7,6 mm)
Thickness	0.06" (1,5 mm)	0.06" (1,5 mm)	0.07" (1,8 mm)	0.07" (1,8 mm)
Tensile Strength	50 lb (23 kg)	50 lb (23 kg)	120 lb (54 kg)	120 lb (54 kg)
Min. Bundle Dia.	0.062" (1,6 mm)	0.062" (1,6 mm)	0.19" (4,8 mm)	0.19" (4,8 mm)
Max. Bundle Dia.	4.00" (102,6 mm)	4.00" (102,0 mm)	4.00" (102,0 mm)	4.00" (102,0 mm)
Items/ Bag	50	500	50	500
Items/ Case	500	2500	500	2500


3M™ Cable Ties

3M™ Cable Ties - Cable Tie Assortment Packs

3M™ Cable Tie Assortment Pack contains 100 of our most commonly used ties. Includes three sizes, four lengths and both colors.

RoHS 2011/65/EU Yes

Agency Approvals 

Country of Origin 



Order No.	UPC	Product Name	Description	Items per Pack	Items per Case
CT06220	051128-59324	3M™ Cable Tie Assortment Pack 06220	3M™ Cable Ties, Assortment Pack, 3 Sizes, 4 Lengths, 2 Natural & Black Colors, 100 in Pack.	100	1000

3M™ Cable Bases and Stackers


3M™ Cable Stackers

3M™ Cable Stackers organize cable runs and aid in identification, putting an end to tangled wires and the potential heating that could occur when cables are held together tightly under a single fastener. Easy installation simplifies compliance with the spacing requirements of the National Electrical Code, article 300-4-(d) and the Canadian Electric Code Part I, Section 12-516. Made from reclaimed plastic.



Cable Tie Type Stacker

Color White

RoHS 2011/65/EU Yes

Country of Origin 




	SI-1	SIFS-1
		
UPC	054007-49554	054007-49918
Product Name	3M™ Cable Stacker SI-1	3M™ Furring Strip Cable Stacker SIFS-1
Description	The 3M™ Cable Stacker SI-1 centers multiple cables on a 2 X 4 framing member.	The 3M™ Furring Strip Cable Stacker SIFS-1 routes, fastens, and supports CATV, telephone, security and instrumentation cables.
Items per Bag	25	25
Items per Case	250	250

3M™ Cable Bases and Stackers

3M™ Cable Tie Mounting Bases

3M™ Cable Tie Bases make mounting wire and cable a quick, easy and secure process. 2-way and 4-way configurations as well as adhesive-backed and screw mount options offer flexible mounting alternatives to meet a variety of applications.

RoHS 2011/65/EU Yes



	CTB2X1BGA-C	CTB1X1BGA-C	CTB75X75NTA-C	CTB75X75BKA-C
UPC	054007-06290	054007-06292	054007-06294	054007-06295
Material	ABS	ABS	Nylon	Nylon
Mount Type	Foam Backed Adhesive	Foam Backed Adhesive (Screw Mount)	Foam Backed Adhesive	Foam Backed Adhesive
Color	Beige	Beige	Natural	Black (UV Resistant)
Length	2.0" (51 mm)	1.0" (25 mm)	0.74" (19 mm)	0.74" (19 mm)
Width	1.0" (25 mm)	1.2" (25 mm)	0.74" (19 mm)	0.74" (19 mm)
Height	0.35" (8,9 mm)	0.15" (3,8 mm)	0.22" (5,6 mm)	0.22" (5,6 mm)
Slot Width	0.21" (5,3 mm)	0.21" (5,3 mm)	0.21" (5,3 mm)	0.21" (5,3 mm)
Slot Height	0.18" (4,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)
Items per Bag	100	100	100	100
Items per Case	500	500	500	500
Country of Origin				
	CTB1X1NTA-C	CTB1X1BKA-C	CTB60X41NTS-C	CTB87X62NTS-C
UPC	054007-06296	054007-06297	054007-95667	054007-95668
Material	Nylon	Nylon	Nylon	Nylon
Mount Type	Foam Backed Adhesive	Foam Backed Adhesive	Screw Mount	Screw Mount
Color	Natural	Black (UV Resistant)	Natural	Natural
Length	0.99" (25 mm)	0.99" (25 mm)	0.60" (15 mm)	0.87" (22 mm)
Width	0.99" (25 mm)	0.99" (25 mm)	0.41" (10 mm)	0.62" (16 mm)
Height	0.22" (5,6 mm)	0.22" (5,6 mm)	0.28" (7,0 mm)	0.38" (10 mm)
Slot Width	0.21" (5,3 mm)	0.21" (5,3 mm)	0.21" (5,3 mm)	0.35" (8,9 mm)
Slot Height	0.06" (1,5 mm)	0.06" (1,5 mm)	0.06" (1,5 mm)	0.10" (2,5 mm)
Items per Bag	100	100	100	100
Items per Case	500	500	500	500
Country of Origin			-	-

3M™ Hook and Loop Fasteners

3M™ Hook and Loop Fasteners

When your product requires thousands of easy openings and secure closings, eliminate the work and weight of metal closures and choose 3M™ Hook and Loop Fasteners. The product forms a secure bond when the stiff hooks of one side mesh with pliable loops on the other.



RoHS 2011/65/EU Yes

Order No.	UPC	Product Name	Description	Rolls per Case
SJ-3526N-Hook-Black-1-1/2	021200-86383	3M™ Fastener Hook SJ3526	Hook (Black) 1 1/2"x50 yd	2
SJ3526N-White-2"x50yd	021200-86247	3M™ Fastener Hook SJ3526	Hook (White) 2"x50yd	2
SJ3527N-1"x50yd-White	021200-86253	3M™ Fastener Loop SJ3527	Loop (White) 1"x50 yd Bulk	3
SJ3527N-2"x50yd-Black	021200-86255	3M™ Fastener Loop SJ3527	Loop (Black) 2"x50 yd Bulk	2
SJ3527N-2"x50yd-White	021200-86256	3M™ Fastener Loop SJ3527	Loop (White) 2"x50 yd Bulk	2
SJ3526N-Beige-1"x50yd	021200-86242	3M™ Fastener Hook SJ3526	Hook (Beige) 1"x50yd	3
SJ3526N-Beige-2"x50yd	021200-86246	3M™ Fastener Hook SJ3526	Hook (Beige) 2"x50yd	2
SJ3526N-Beige-5/8"x50yd	021200-86239	3M™ Fastener Hook SJ3526	Hook (Beige) 5/8"x50yd	4
SJ3401-1"x50yd-Black	021200-62538	3M™ Fastener Loop SJ3401	Loop (Black) 1"x50 yd	12
SJ3401-1"x50yd-White	021200-62539	3M™ Fastener Loop SJ3401	Loop (White) 1"x50 yd	12
SJ3401-2"x50yd	021200-62544	3M™ Fastener Loop SJ3401	Loop (Black) 2"x50 yd	6
SJ3402-1"x50yd-Black	021200-62553	3M™ Fastener Hook SJ3402	Hook (Black) 1"x50 yd	12
SJ3402-1"x50yd-White	021200-62554	3M™ Fastener Hook SJ3402	Hook (White) 1"x50 yd	12
SJ3402-2"x50yd	021200-62559	3M™ Fastener Hook SJ3402	Hook (Black) 2"x50 yd	6
SJ3402-3/4"x50yd-Black	021200-62550	3M™ Fastener Hook SJ3402	Hook (Black) 3/4"x50 yd	16
SJ-3522	021200-86236	3M™ Fastener Plasticizer Resistant Hook SJ3522	Hook (Black) 1"x50 yd	3
SJ-3523	021200-86238	3M™ Fastener Plasticizer Resistant Loop SJ3523	Loop (Black) 1"x50 yd	3
SJ3526N-2"x50yd	021200-86245	3M™ Fastener Hook SJ3526	Hook (Black) 2"x50 yd	2
SJ3526N-Black-5/8"x50yd	021200-86240	3M™ Fastener Hook SJ3526	Hook (Black) 5/8"x50yd	4
SJ-3526N-Hook-Black-1"	021200-86243	3M™ Fastener Hook SJ3526	Hook (Black) 1"x50 yd	3
SJ-3526N-Hook-White-5/8"	021200-86241	3M™ Fastener Hook SJ3526	Hook (White) 5/8"x50 yd	4
SJ3527N-Beige-1"x50yd	021200-86251	3M™ Fastener Loop SJ3527	Loop (Beige) 1"x50yd	3
SJ3527N-Beige-2"x50yd	021200-86254	3M™ Fastener Loop SJ3527	Loop (Beige) 2"x50yd	2
SJ3527N-Beige-5/8"x50yd	021200-86248	3M™ Fastener Loop SJ3527	Loop (Beige) 5/8"x50yd	4
SJ3527N-Black-1.5"x50yd	021200-86167	3M™ Fastener Loop SJ3527	Loop (Black) 1.5"x50yd	2
SJ-3527N-Loop-Black-1"	021200-86252	3M™ Fastener Loop SJ3527	Loop (Black) 1"x50 yd	3
SJ3527N-White-5/8"x50yd	021200-86250	3M™ Fastener Loop SJ3527	Loop (White) 5/8"x50yd	4
SJ-3532N-Hook-Black-1"	021200-86259	3M™ Fastener Hook SJ3532	Hook (Black) 1"x50 yd	3
SJ-3533N-Loop-Black-1"	021200-86266	3M™ Fastener Loop SJ3533	Loop (Black) 1"x50 yd	3
SJ-3571-1"x50yd-Black	021200-86285	3M™ Fastener Loop SJ3571	Loop (Black) 1"x50 yd	3
SJ3571-1"x50yd-White	021200-87277	3M™ Fastener Loop SJ3571	Loop (White) 1"x50 yd	3
SJ3571-5/8"x50yd-Black	021200-86289	3M™ Fastener Loop SJ3571	Loop (Black) 5/8"x50 yd	4
SJ3571-White-2"x50yd	021200-86467	3M™ Fastener Loop SJ3571	Loop (White) 2"x50yd	2
SJ-3572-1"x50yd-Black	021200-86286	3M™ Fastener Hook SJ3572	Hook (Black) 1"x50 yd	3
SJ3572-2"x50yd-Black	021200-86377	3M™ Fastener Hook SJ3572	Hook (Black) 2"x50 yd	2
SJ3572-5/8"x50yd-Black	021200-86290	3M™ Fastener Hook SJ3572	Hook (Black) 5/8"x50 yd	4

3M™ Hook and Loop Fasteners

3M™ Scotchmate™ Reclosable Fasteners

When your project requires the flexibility of many easy openings and secure closings, but you don't want the weight of metal closures try 3M™ Hook and Loop Fasteners in mini-pack sizes. Available in various adhesive options and product sizes in a quantity appropriate for small projects and testing.

RoHS 2011/65/EU Yes



Order No.	UPC	Product Name	Description	Rolls per Case
MP3401/MP3402-Black	051131-06465	3M™ Scotchmate™ Reclosable Fastener MP3401	Reclosable Fastener (Black) 1"x5 yd	5
MP3401/MP3402-White	051131-06464	3M™ Scotchmate™ Reclosable Fastener MP3402	Reclosable Fastener (White) 1"x5 yd	5
MP-3526/27N-Black	051131-06481	3M™ Scotchmate™ Reclosable Fastener MP3526/MP3527	Hook and Loop Fastener (Black) 1"x5 yd Mini Pack (Roll)	5
MP-3526/27N-White	051131-06488	3M™ Scotchmate™ Reclosable Fastener MP3526/MP3527	Hook and Loop Fastener (White) 1"x5 yd Mini Pack (Roll)	5

3M™ Dual Lock™ Fasteners

3M™ Dual Lock™ Fasteners

Strong. Hidden. Removable. 3M™ Dual Lock™ Reclosable Fasteners are a fastening solution that can replace screws, bolts and rivets. The fasteners contain hundreds of mushroom-shaped stems that audibly "SNAP" together to form a secure attachment with strong adhesive backings that adhere to your substrate.

RoHS 2011/65/EU Yes




Order No.	UPC	Product Name	Description	Rolls per Case
MP-3541/42-Black	051131-06483	3M™ Dual Lock™ Reclosable Fastener MP3541/MP3542 400/170	Reclosable Fastener (Black) 400 stems per square inch, 1"x5 yd	5
MP-3551/52-Black	051131-06484	3M™ Dual Lock™ Reclosable Fastener MP3551/MP3552 400/170	Reclosable Fastener (Black) 400 stems per square inch., 1"x5 yd	5
MP-3560-Clear	051131-06463	3M™ Dual Lock™ Reclosable Fastener MP3560 250	Reclosable Fastener (Clear) 250 stems per square inch, 1"x5 yd	5
SJ-3463	021200-24993	3M™ Dual Lock™ Reclosable Fastener SJ3463 400	Reclosable Fastener (Black) rigid backed circle with hole, 400 stems per square inch, 1 3/16" diameter with 0.16 in hole.	1000
SJ3540-1"x50yd-Black	021200-65812	3M™ Dual Lock™ Reclosable Fastener 250 SJ3540	Reclosable Fastener (Black) 250 stems per square inch, 1"x50 yd	2
SJ-3541-1"x50yd-Black	021200-86277	3M™ Dual Lock™ Reclosable Fastener 400 SJ3541	Reclosable Fastener (Black) 400 stems per square inch, 1"x50 yd	2
SJ-3542-1"x50yd-Black	021200-86309	3M™ Dual Lock™ Reclosable Fastener SJ3542 170	Reclosable Fastener (Black) 170 stems per square inch, 1"x50 yd	2
SJ-3560-1"x50yd-Clear	021200-86282	3M™ Dual Lock™ Reclosable Fastener 250 SJ3560	Reclosable Fastener (Clear) 250 stems per square inch, 1"x50 yd	2
SJ-3748	021200-63628	3M™ Dual Lock™ Reclosable Fastener 400 SJ3748 Black	Pop-in, Christmas tree style reclosable fastener with a 16.2 mm stud, 400 stems per square inch, 1 inch x 1 inch.	5000
SJ-3755	021200-24129	3M™ Dual Lock™ Reclosable Fastener 250 SJ3755 Black	Black, polypropylene reclosable fastener with rigid backing, rigid backed circle with one hole, 250 stems per square inch, 1 1/8 inch (28.5 mm) outside diameter.	1000
SJ-3762	021200-24131	3M™ Dual Lock™ Reclosable Fastener 400 SJ3762 Black	Black, polypropylene reclosable fastener with rigid backing, rigid backed circle with one hole, 400 stems per square inch, 1 1/8 inch (28.5 mm) outside diameter.	1000
SJ-3767	021200-24128	3M™ Dual Lock™ Reclosable Fastener SJ3767 Black	Black, polyolefin plastic reclosable square fastener with two counter-sunk holes, 400 stem per square inch, 1 1/2 inch (38 mm).	1000

3M™ Dual Lock™ Fasteners

3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570

Low to medium temperature performance. Bonds well to metals (aluminum, stainless steel), glass, many plastics (polypropylene, polyethylene, polycarbonate, ABS) powder coated paints and medium to low surface energy materials. Designed for indoor use. Products include SJ4570 and SJ4575.

RoHS 2011/65/EU Yes



Order No.	UPC	Product Name	Description	Rolls per Case
SJ4570-1"x50yd-Clear	021200-44883	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 1 in x 50 yd 0.105 in (2,7 mm).	2
SJ4570-2"x50yd-Clear	021200-46070	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 2 in x 50 yd 0.105 in (2,7 mm).	1
SJ4570-3/4"x50yd-Clear	021200-46239	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 3/4 in x 50 yd 0.105 in (2,7 mm).	2
SJ4570-4"x50yd-Clear	021200-46071	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 4 in x 50 yd 0.105 in (2,7 mm).	1
SJ4570-4"x75yd-Clear	021200-46196	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 4 in x 75 yd 0.105 in (2,7 mm).	1
SJ4570-5/8"x50yd-Clear	021200-45075	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 5/8 in x 50 yd 0.105 in (2,7 mm).	3