

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [82-22-6110](#)  
**Status:** **Active**  
**Description:** 2.54mm Pitch Round Conductor Flat Cable - 22 AWG (7 x 30) Stranded, Tinned, 10 Circuits, Reel 30.48m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR61126  
 UL E61522

**General**

Product Family Cable  
 Series [7560](#)  
 Crimp Quality Equipment Yes  
 Geographic Area Asia  
 Product Name Ribbon  
 UPC 800754370738

**Physical**

Cable Length 30.48m  
 Circuits (Loaded) 10  
 Insulation PVC  
 Net Weight 1595.000/g  
 Packaging Type Reel  
 Pitch - Termination Interface 2.54mm  
 Temperature Range - Operating -20°C to +105°C  
 Wire Size AWG 22  
 Wire/Cable Type (7x30) Stranded, Tinned

**Electrical**


Current - Maximum per Contact N/A  
 Voltage - Maximum 300V

**Material Info**

Old Part Number 7560-10-100B

**Reference - Drawing Numbers**

Sales Drawing SD-7560-001



**EU RoHS**

**ELV and RoHS  
 Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Low-Halogen**

**China RoHS**



**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[7560Series](#)

**Use With**

70400 C-Grid SL™ IDT Connector  
 Assembly. 70475 SL™ IDT Connector  
 Assembly. 7720 KK® IDT Double Cantilever  
 Contact

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**