

638164

European Region

BRIGHT

- Provides 80 lumens of light in high mode
- Uses premium Nichia® LED technology.



VERSATILE

- Spot, flood, strobe and area lights plus night vision LEDs
- Push button switch cycles modes



ECONOMICAL

- Runs 26 hours on one set of batteries in high mode
- LEDs never need replacing



WEATHERPROOF

- Meets IEC 60529 IPX4 standards
- Continues to operate after exposure to splashing water from all directions



EUROPEAN REGION

Lightweight, versatile and comfortable, the Energizer® 6-LED Headlight is perfect for electrical, plumbing, HVAC or other work that requires both hands. It puts light where you are looking and has a swivel adjustment with ratchet positioning for accurate aim.

Variable light sources allow you to choose the best illumination for the job – area, flood, spot or night vision. Also, this light mounts securely to hard hats or can be comfortably worn around the head for long periods of time.



Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation: Energizer
6-LED Headlight

SAP: 638164

Colour: Orange

Power Source: Three "AAA"

IEC: LR03

Lamp: Four White LEDs, Two Red LEDs

Lamp Life (hr): Lifetime

Mode:	4 White	2 Spot	2 Flood	Red
Lamp Output (lumens):	80	60	30	4
Run Time (h:mm):	8:30	13	26	25
Beam Distance (m):	19	19	5	-


Weight: 87.5 grams with batteries

Dimensions (mm): 45 x 40 x 73

Performance:

Run Time

Continuous Drain to
End of Useable Light (21° C)



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a claim or warranty
©Energizer / All Rights Reserved