

MAINNING CO., LTD.

Office: Room No.1105, Pingan Mansion, No.396 Kaiming Street, Ningbo, China
Tel:0086-574-87288314,87255118
E-mail: mainning@mail.nbptt.zj.cn

P. C. : 315000

MAINNING


Product Code: 8442 Belden Equivalent

Page:1/1

1.--/ CONSTRUCTION

Item	Description
1. Conductor	22AWG(7/0.254mm) stranded Tinned Copper
2. Insulation	Colour code PVC, Nominal thickness: 0.38mm; Colour code: Black, Red
Pair Number	1 Pair, twisted pair
3. Jacket	Grey PVC, Nominal thickness: 0.64mm; Overall Diameter: 4.32+/-0.20mm

2.--/ DESIGN



3.--/ CHARACTERISTICS

Nominal Capacitance	30.000pF/Feet
Nominal Conductor DCR	15.600 Ohm/1000Feet
Nominal Velocity of Propagation	%
Nominal Impedance	Ohms

4.--/ PACKING

Description	Size(Flange Dia. X Width)
500M Plywood Drum packing	mm X mm
1000M Plywood Drum packing	370mm X 245mm

Drawn by	Date	Checked	Approved
Xu Hualing	8th Aug., 2003	Wang Yangying	郑松林
MAINNING CO., LTD.			
Drawing Number : 84420			
Revision Level: Revised		Page 1 of 1	