

Data sheet WSF 80

Weller part no.	T0051384899
Description	Pistol grip soldering iron with manual solder feed
Type	WSF 80
Supply voltage	230V 50Hz
Supply Indication	Red neon light
Max power	80W variable 0 – 100%
Max temperature	550 C at 100% power rating
Mains lead	1.2 metre long fitted with Schuko mains plug
Solder feed tube	variable position
Traction control	To compensate for solder diameter variance
Trigger adjustment	for variable solder length delivery
Viewing window	To facilitate solder loading into the delivery tube
Solder delivery tubes	1 x 1.00mm and 1 x 1.5mm
Solder tip	Fitted with SF25 (2.5mm chisel tip)
Uses	SF series tips