

Spring 2014

FLUKE®

FLUKE SPECIALS


**Visual IR
Thermometer
Fluke VT04**

**Special promotions
on all Fluke Multifunction
Installation Testers**



The Most Trusted Tools in the World.

Temperature solutions: fit for your job, fit for your pocket



Hot/cold markers



**Fluke 62MAX
Fluke 62MAX+**

Fluke 561

**Fluke 566
Fluke 568**

Fluke 572-2

**Fluke VT04
Fluke VT02**

- Min/max/avg/dif
- Dust/water resistant (IP54)

- Combined IR + contact
- HVAC applications

- Data logging
- Combined IR + contact

- Data logging
- Hi/Lo alarm
- Min/max/avg/dif
- IR + contact

- Image storage
- Analysis software

NEW PRICES!

Exact spot positioning

Heat map

Features	62MAX	62MAX+	561	566	568	572-2	VT02	VT04
		Infrared thermometer		Multipurpose thermometer			High temperature infrared thermometer	Visual IR thermometer
Temperature range	-30 to 500 °C	-30 to 650°C	-40 to 550 °C	-40 to 650 °C	-40 to 800 °C	-30 to 900 °C	-10 to 250 °C	-10 to 250 °C
D:S	10:1	12:1	12:1	30:1	50:1	60:1	6:1	9:1
Laser sighting	Single laser	Dual laser	Single-point laser	Single-point laser	Single-point laser	Offset dual laser	No laser necessary	No laser necessary
	£ 84	£ 100	£ 131	£ 339	£ 429	£ 515	£ 395	£ 595



Fluke CNX™ Wireless Test Tools. Safer. Easier. Faster.



Use Wirelessly



Use as stand alone



Use as data logger

Your tools - connected.

Take readings quicker. Solve problems faster. Fluke CNX™ wireless test tools work together to help you troubleshoot faster. With the CNX™ team, measurements are:

- Remote
- Simultaneous
- Recordable

Connect any of the CNX™ Modules to your test point, and view the results up to 20 meters away on the CNX™ Wireless Multimeter. You'll save time, with less run-around collecting multiple measurements.



Fluke CNX i3000
iFlex™ AC Current Clamp
£ 129



Fluke CNX 3000
Wireless Multimeter
£ 259



Fluke CNX t3000
K-type Temperature
£ 109



Fluke CNX v3000
AC Voltage
£ 109



Fluke Ti100 series
Thermal Imager
From £ 1650



Fluke CNX a3000
AC Current Clamp
£ 109



Fluke CNX pc3000
PC adapter
£ 39

Fluke 6200-2 and 6500-2 Portable Appliance Testers

NEW

Perform more tests each day! The low weight, small size, one-touch solutions.

Improved auto-test capabilities to help you increase the number of tests completed each day. Designed to work faster without compromising safety – yours or your customer's.

- 'One-touch' testing: dedicated key per test
- Save time: pre-set pass/fail levels
- Easy reading: large backlit display
- Rapid data entry: integral keyboard
- Back-up data storage and transfer: additional USB memory drive
- Pre-set, auto-test sequences

NEW colour Dot Matrix Display:

Superior visibility and viewing angle

NEW 250V Insulation Test

NEW 110V Test Functionality

NEW RCD Test

Optional accessories:

- DMS 0702/PAT software
- SP-SCAN-6000 barcode scanner
- SP6000 printer

Also available as a kit.



Fluke 6200-2

£ 873



Fluke 6500-2

£ 1244

Fluke TestGuide

The NEW TestGuide app shows electricians in short and clear steps what the actions are for the most common measurements, what to look at and how to interpret the results. You will also find background articles and in-depth application notes which can be downloaded or send to your email.

Free Download!

www.fluke.co.uk/testguide



NEW



Special promotions New Fluke Multifunction Installation Tester Kits

PROMOTION

Fast, lightweight, easy to use, robust and reliable installation tester.
Now all models with great offers!

- Fast high current loop test
- Reliable 3-wire loop test
- No complex multi-level menus: rotary dial clearly indicates selected function
- Easy test lead compensation: Zero adapter
- Extended memory*
- mΩ resolution: loop & line resistance*
- Variable RCD current mode for customised settings
- Test smooth DC sensitive RCDs*
- PASS/FAIL indication for RCD tests

Fluke 1652C / Fluke T110 kit



**Fluke 1652C +
FREE T110**

Now with **FREE Cabinet key****



**Fluke 1652C-
TPOLEKIT
£ 947**

Fluke 1653B / Software / Fluke T130 kit



**Fluke 1653B +
FREE Software & T130**

Now with **FREE Cabinet key****



**Fluke 1653B-
TPOLEKIT/D
£ 1159**

Fluke 1654B / Software / Fluke T150 kit



**Fluke 1654B +
FREE Software & T150**

Now with **FREE Cabinet key****



**Fluke 1654B-
TPOLEKIT/D
£ 1293**

* 1654B only

** Free Cabinet key offer valid until 30.06.2014, only available direct from Fluke by using special offer voucher, proof of purchase required. Go to www.fluke.co.uk/promotions to download the voucher and view full terms and conditions or contact Fluke directly.

Fluke Clamp Meters: Readings you can rely on

True RMS

Wire in tight spaces - panels out of reach - extra large conductors.
Noise free measurements for every workspace.



Fluke iFlex™
£ 89



Now with FREE 2AC VoltAlert*



	Fluke 365	Fluke 323	Fluke 324	Fluke 325	Fluke 373	Fluke 374	Fluke 375	Fluke 376
Jaw opening	18 mm	30 mm	30 mm	30 mm	32 mm	34 mm	34 mm	34 mm
Current AC TRMS	200 A	400 A	400 A	400 A	600 A	600 A	600 A	1000 A
Current DC	200 A	-	-	400 A	-	600 A	600 A	1000 A
Voltage AC	600 V	600 V	600 V	600 V	600 V	600 V	600 V	1000 V
Voltage DC	600 V	600 V	600 V	600 V	600 V	600 V	600 V	1000 V
Continuity	●	●	●	●	●	●	●	●
Resistance	●	●	●	●	●	●	●	●
Capacitance	-	-	●	●	●	●	●	●
Frequency	-	-	-	●	-	-	●	●
Contact temperature	-	-	-10 ... 400°C	-10 ... 400°C	-	-	-	-
In-rush	-	-	-	-	●	●	●	●
i-Flex	-	-	-	-	-	optional	optional	included (18")
Price	£ 199	£ 99	£ 118	£ 159	£ 176	£ 265	£ 317	£ 379

FREE 2AC *

* Free 2AC offer valid until 30.06.2014, only available direct from Fluke by using special offer voucher, proof of purchase required. Go to www.fluke.co.uk/promotions to download the voucher and view full terms and conditions or contact Fluke directly.



Check our **NEW**
electrician's toolbelt page!
www.fluke.co.uk/toolbelt

Earth ground testing

Simpler and Faster.

The Fluke 1623-2 and 1625-2 earth ground testers are accurate, safe and very easy to use. Perform basic earth ground tests up to the most advanced tests. Several test methods provide quick and precise impedance measurements:

- 3-and-4-pole Fall-of-Potential
- 2-pole
- selective
- stakeless

NEW USB Data Storage and transfer
NEW larger display:

Automatic Frequency Control (AFC)

NEW world class accessories:

- Easy to use reels
- Heavy-duty stakes
- Colour coded wires (faster set up)



Fluke 1623-2
£ 999



Fluke 1625-2
£ 1599

NEW

Fluke 110 series Digital Multimeters

Economic investment in accuracy, simple operation for easy and fast measurements.



PROMOTION

Now with **FREE 2AC VoltAlert***

3 Years Warranty!
Keep your Fluke meter up and running

True RMS

	Fluke 113	Fluke 114	Fluke 115	Fluke 116	Fluke 117
True RMS readings	●	●	●	●	●
Display backlight	●	●	●	●	●
VoltAlert™, Non-contact voltage detection	-	-	-	-	●
Built-in thermometer (probe included)	-	-	-	●	-
LoZ (low input impedance)	-	●	-	●	●
Microamps to test flame sensors	-	-	-	●	-
Frequency, capacitance, Diode test	-/●/●	-	●/●/●	●/●/●	●/●/●
Recommended AC current clamp**	-	i200s	i200s	i200s	i200s
Recommended pouch	C25	C25	C25	C25	C25
CAT III	600V	600V	600V	600V	600V
Price	£ 109	£ 128	£ 151	£ 174	£ 180
			FREE 2AC *		FREE 2AC *

* Free 2AC offer valid until 30.06.2014, only available direct from Fluke by using special offer voucher, proof of purchase required. Go to www.fluke.co.uk/promotions to download the voucher and view full terms and conditions or contact Fluke directly.

** for AC current 1 - 200 A

PLAY AND WIN!

Play the Electrician Game and win rugged and innovative Fluke tools!

www.fluke.co.uk/game



Laser Distance Meters

Fluke laser distance meters will become the next essential item on your toolbelt.



Fluke 414D £ 99
Fluke 419D £ 185
Fluke 424D £ 283

VoltAlert™

When the tip of the Fluke VoltAlert AC voltage detector glows red and the unit beeps, you know there is voltage on the line.



Fluke 2AC
£ 19

Two Pole Testers from Fluke

Robust,
 easy, fast
 and safe.



Fluke T150
£ 109

Fluke T130
£ 89

Fluke T110
£ 56

Fluke T90
£ 37

T5/H5/1AC Kit

- Fluke T5-1000 Electrical Tester
- Fluke 1AC-II Volt Alert
- Fluke H5 holster



£ 142
 Save up to
20%*

T5-600/62MAX+/1AC Kit

- Fluke T5-600 Electrical Tester
- Fluke 62MAX+ IR Thermometer
- Fluke 1AC-II Volt Alert
- C115 soft meter case



£ 197
 Save up to
33%*

62MAX+/323/1AC Kit

- Fluke 62MAX+ IR Thermometer
- Fluke 323 Clamp Meter
- Fluke 1AC-II Volt Alert
- C115 Soft meter case



£ 200
 Save up to
25%*

414D/62MAX+ Kit

- Fluke 414D Laser Distance Meter
- Fluke 62MAX+ IR Thermometer



£ 150
 Save up to
20%*

* Saving based on the cost of purchasing the individual items separately at manufacturers recommended resale price.

All prices in this leaflet are recommended resale prices only and exclude VAT.
 © Copyright 2014 Fluke Corporation. All rights reserved.
 Specifications are subject to change without notice. All actions are valid until 30.06.2014.
 Issue Spring 2014. Printed in the Netherlands.

Look for more details on
Fluke products and special promotions
 at www.fluke.co.uk/promotions

T5/7-600 Electrical Testers 1AC II VoltAlert

FLUKE®



Fluke T5-1000

Fluke 7-600



New



Fluke 1AC II

Included Accessories

T5-600 and T5-1000:

TP4 4 mm detachable probes (detachable GS38 probes for the UK) and instruction sheet

Fluke 7-600:

TL75 Hard Point Test Leads, a 9 volt battery (installed) and owner's manual.

Ordering Information

Fluke T5-600	Electrical Tester
Fluke T5-1000	Electrical Tester
Fluke 7-600	Electrical Tester
Fluke 1AC II	VoltAlert
Fluke 1AC II 5PK	VoltAlert (5-pack)

The fast and easy solution to basic electrical testing

Fluke T5-600 and T5-1000 Voltage, Continuity and Current Testers

The Fluke T5 testers let you check voltage, continuity and current with one compact tool. Select volts, ohms or current and the instrument does the rest. Model T5-600 measures 600 volts AC/DC, model T5-1000 is designed for 1000 volts. OpenJaw™ current technology lets you check current up to 100 A, without breaking the circuit. The optional H5 holster keeps the test probes and leads ready to test and lets you clip the T5 onto your belt.

7-600 Electrical Tester

The easiest way to check AC/DC continuity and resistance is with the Fluke 7-600. The Fluke 7-600 can measure up to 600V AC or DC. Just switch the unit on and it will automatically switch to the correct setting. An input impedance of 2KΩ distinguishes real voltage from voltage caused by leakage or capacitive coupling.

Features and Specifications

	T5-600	T5-1000	7-600
Display Count	1000	1000	4000
Automatic Selection	●	●	●
Continuity and Beeper	●	●	●
Sleep Mode	●	●	●
AC Voltage	600V	1000V	600V
DC Voltage	600V	1000V	600V
AC Current	100A	100A	
Resistance	1000Ω	1000Ω	400Ω
Safety range	600V CAT III	1000V CAT III	600V CAT III

T5-600/T5-1000

Battery life: 400 hours
Size (HxWxD): 203 mm x 51 mm x 30.5 mm
Weight: 0.38 kg
Two year warranty

7-600

Battery life: Alkaline, 650 hours continuous, sleep mode
Size (HxWxD): 142.3 mm x 70.5 mm x 34.6 mm
Weight: 0.286 kg
Two year warranty

Fluke 1AC II VoltAlert™

The Fluke VoltAlert AC voltage detector is very easy to use – just touch the tip to a terminal strip, outlet or cord. When the tip glows red and the unit beeps, you know there is voltage on the line.

- It continually tests its battery and its circuit integrity with a periodic double flash visual indication.
- Highest safety rating: CAT IV 1000 V
- Detects voltage without metallic contact

Operating range: 200 – 1000 V AC
Batteries: Two AAA Alkaline
Size (H): 148 mm
Two Year Warranty

Fluke 1AC II VoltAlert™ 5-pack
 • Buy 4 get 1 FREE



Recommended Accessories T5



H5

ACC-T5-KIT

AC285

TP38

L210