

## MINIATURE LAMP (93) Details



<b>Part #</b>	<b>93</b>				
<b>Description</b>	<b>S8 SC BAY 12.8V 1.04A 15CP</b>				
<b>Bulb Shape</b>	S-8	<b>Filament</b>	C-6	<b>Base Style</b>	S.C. Bayonet (BA15s)
<b>Glass Diameter (in)</b>	1.04	<b>MOL<sup>†</sup> (in)</b>	2.00	<b>LCL<sup>††</sup> (in)</b>	1.13
<b>Glass Diameter (mm)</b>	26.5	<b>MOL (mm)</b>	50.80	<b>LCL (mm)</b>	28.70
<b>Volts</b>	12.8	<b>MSCP<sup>‡</sup></b>	15	<b>Avg Life Hrs</b>	700
<b>Watts</b>	13.312	<b>Amps</b>	1.04	<b>RoHS Compliant</b>	Yes

**† MOL (Maximum Overall Length):**

The overall length of a lamp, from the top of the shell to the bottom of the base.

**‡ MSCP (Mean Spherical Candlepower):**

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

**†† LCL (Light Center Length):**

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.