



Product Number: 54660

Order Abbreviation: DDL

General Description: 150 watt, tungsten halogen, low to medium voltage with reflector

Product Information	
Abbrev. With Packaging Info.	DDL 20V 24/CS 1/SKU
ANSI Code	DDL
Application	Projector - Microfilm
Average Rated Life (hr)	500
Base	GX5.3 Bipin
Bulb	MR16
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature (K)	3150
Diameter d (in)	2.008
Diameter d (mm)	51.00
Filament	CC-6
Lamp Finish	Clear
Length l (in)	1.486
Length l (mm)	38.1
Length l max. (in)	1.486
Length l max. (mm)	38.1
Maximum Overall Length - MOL (in)	1.689
Maximum Overall Length - MOL (mm)	43.3
Nominal Voltage (V)	20.00
Nominal Wattage (W)	150.00
Operating Position	Any
Reflector Coating	WHITE
Type of Current	AC
Working Distance a (in)	7.430
Working Distance a (mm)	190.5