

RoHS
Compliant



Defence Standard Part6 – Type 2:

Construction:

Conductor	Tinned Copper
Insulation	Type 2 PVC compound to BS 7655-3.2

Standards / Conformances:

Def Stan 61-12 (Part 6) and BS 4808: Part 2, where applicable.

Electrical Characteristics:

Rated Voltage (V) : 1000V AC rms
Min. Insulation Resistance at 20°C (MΩ/km) : 50
Rated Conductor Temperature (°C) : 85

Physical Characteristics:

Conductor Size (mm)	Insulation Diameter (mm)		Max. Conductor DC Resistance at 20°C (Ω/km)
	Min.	Max.	
1/0.4	0.9	1.1	145
1/0.6	1.1	1.3	64.1
1/0.9	1.4	1.6	28.5
7/0.2	1.1	1.3	88
10/0.1	0.95	1.15	≤255.7
16/0.2	1.45	1.65	38.2
24/0.2	1.95	2.15	25.5

Defence Standard Part6 – Type 3:

Construction:

Conductor	Tinned Copper
Insulation	Type TI 1 PVC compound to BS EN 50363-3

Standards / Conformances:

Def Stan 61-12 (Part 6) and BS 4808: Part 2, where applicable.

Electrical Characteristics:

Rated Voltage (V) : 1,000V AC rms
 Min. Insulation Resistance at 20°C (MΩ/km) : 10
 Rated Conductor Temperature (°C) : 85

Physical Characteristics:

Conductor Size (mm)	Insulation Diameter (mm)		Max. Conductor DC Resistance at 20°C (Ω/km)
	Min.	Max.	
16/0.2	2	2.25	38.2
24/0.2	2.2	2.45	25.5
32/0.2	2.4	2.65	19.1
63/0.2	2.9	3.15	9.7

Part Number Table

Description	Part Number
Wire, 100m, 10/0.1mm, Copper, Black	MC10/0.1 TYPE 2 BLACK 100M
Wire, Brown, 10/0.1mm, 100m	MC10/0.1 TYPE 2 BROWN 100M
Wire, 100M, 10/0.1mm, Copper, Red	MC10/0.1 TYPE 2 RED 100M
Wire, Orange, 10/0.1mm, 100m	MC10/0.1 TYPE 2 ORANGE 100M
Wire, Yellow, 10/0.1mm, 100m	MC10/0.1 TYPE 2 YELLOW 100M
Wire, Green, 10/0.1mm, 100m	MC10/0.1 TYPE 2 GRN 100M
Wire, Blue, 10/0.1mm, 100m	MC10/0.1 TYPE 2 BLUE 100M
Wire, Pink, 10/0.1mm, 100m	MC10/0.1 TYPE 2 PINK 100M

Part Number Table

Description	Part Number
Wire, Grey, 10/0.1mm, 100m	MC10/0.1 TYPE 2 GREY 100M
Wire, White, 10/0.1mm, 100m	MC10/0.1 TYPE 2 WHT 100M
Wire, Violet, 10/0.1mm, 100m	MC10/0.1 TYPE 2 VIOLET 100M
Wire, Red, 10/0.1mm, 500m	MC10/0.1 TYPE 2 RED 500M
Wire, Yellow, 10/0.1mm, 500m	MC10/0.1 TYPE 2 YEL 500M
Wire, Green, 10/0.1mm, 500m	MC10/0.1 TYPE 2 GRN 500M
Wire, Blue, 10/0.1mm, 500m	MC10/0.1 TYPE 2 BLUE 500M
Wire, 10/0.1 White 500m	MC10/0.1 TYPE 2 WHT 500M
Wire, 500M, 7/0.2mm, Copper, Black	MC7/0.2 TYPE 2 BLK 500M
Wire, Brown, 7/0.2mm, 500m	MC7/0.2 TYPE 2 BRN 500M
Wire, 500M, 7/0.2mm, TC, Red	MC7/0.2 TYPE 2 RED 500M
Wire, Orange, 7/0.2mm, 500m	MC7/0.2 TYPE 2 ORANGE 500M
Wire, Yellow, 7/0.2mm, 500m	MC7/0.2 TYPE 2 YEL 500M
Wire, Green, 7/0.2mm, 500m	MC7/0.2 TYPE 2 GRN 500M
Wire, Blue, 7/0.2mm, 500m	MC7/0.2 TYPE 2 BLUE 500M
Wire, Violet, 7/0.2mm, 500m	MC7/0.2 TYPE 2 VIOLET 500M
Wire, Grey, 7/0.2mm, 500m	MC7/0.2 TYPE 2 GREY 500M
Wire, White, 7/0.2mm, 500m	MC7/0.2 TYPE 2 WHT 500M
Wire, Pink, 7/0.2mm, 500m	MC7/0.2 TYPE 2 PINK 500M
Wire, Red/Black, 7/0.2mm, 100m	MC6A-7/0.2T2-RDBK-100
Wire, Red/Brown, 7/0.2mm, 100m	MC6A-7/0.2T2-RDBN-100
Wire, Red/Green, 7/0.2mm, 100m	MC6A-7/0.2T2-RDGN-100
Wire, Red/Blue, 7/0.2mm, 100m	MC6A-7/0.2T2-RDBE-100
Wire, Orange/Black, 7/0.2mm, 100m	MC6A-7/0.2T2-OEBK-100
Wire, Orange/Red, 7/0.2mm, 100m	MC6A-7/0.2T2-OERD-100
Wire, Yellow/Black, 7/0.2mm, 100m	MC6A-7/0.2T2-YWBK-100
Wire, Yellow/Red, 7/0.2mm, 100m	MC6A-7/0.2T2-YWRD-100
Wire, Yellow/Green, 7/0.2mm, 100m	MC6A-7/0.2T2-YWGN-100
Wire, Green/Red, 7/0.2mm, 100m	MC6A-7/0.2T2-GNRD-100
Wire, Violet/Red, 7/0.2mm, 100m	MC6A-7/0.2T2-VTRD-100
Wire, Grey/Black, 7/0.2mm, 100m	MC6A-7/0.2T2-GYBK-100
Wire, Grey/Blue, 7/0.2mm, 100m	MC6A-7/0.2T2-GYBE-100
Wire, White/Black, 7/0.2mm, 100m	MC6A-7/0.2T2-WEBK-100
Wire, White/Red, 7/0.2mm, 100m	MC6A-7/0.2T2-WERD-100
Wire, Pink/Black, 7/0.2mm, 100m	MC6A-7/0.2T2-PKBK-100

Part Number Table

Description	Part Number
Wire, Green/Yellow, 7/0.2mm, 100m	MC6A-7/0.2T2-GNYW-100
Wire, Purple/Red, 7/0.2mm	7/0.20 PUR/RED
Wire, Green/Yellow, 7/0.2mm, 500m	7/0.20 GRN/YELL
Wire, 100M, 16/02mm ² , Copper, Black	MC16/0.2 TYPE 2 BLK 100M
Wire, 100M, 16 × 0.2mm, Copper, Brown	MC16/0.2 TYPE 2 BRN 100M
Wire, 100M, 16/02mm ² , Copper, Red	MC16/0.2 TYPE 2 RED 100M
Wire, 16/0.2mm, Copper, Orange, 100m	MC16/0.2 TYPE 2 ORNG 100M
Wire, 100M, 16/0.2mm, Copper, Yellow	MC16/0.2 TYPE 2 YEL 100M
Wire, 16/0.2mm, Copper, Green, 100m	MC16/0.2 TYPE 2 GRN 100M
Wire, 100m, 16/0.2mm ² , Copper, Blue	MC16/0.2 TYPE 2 BLUE 100M
Wire, Violet, 16/0.2mm, 100m	MC16/0.2 TYPE 2 VIOLET 100M
Wire, Grey, 16/0.2mm, 100m	MC16/0.2 TYPE 2 GREY 100M
Wire, 100m, 16/0.2mm, Copper, White	MC16/0.2 TYPE 2 WHT 100M
Wire, Pink, 16/0.2mm, 100m	MC16/0.2 TYPE 2 PINK 100M
Wire, Black, 16/0.2mm, 500m	MC16/0.2 TYPE 2 BLK 500M
Wire, Brown, 16/0.2mm, 500m	MC16/0.2 TYPE 2 BRN 500M
Wire, Red, 16/0.2mm, 500m	MC16/0.2 TYPE 2 RED 500M
Wire, Orange, 16/0.2mm, 500m	MC16/0.2 TYPE 2 ORNG 500M
Wire, Yellow, 16/0.2mm, 500m	MC16/0.2 TYPE 2 YEL 500M
Wire, Green, 16/0.2mm, 500m	MC16/0.2 TYPE 2 GRN 500M
Wire, Blue, 16/0.2mm, 500m	MC16/0.2 TYPE 2 BLUE 500M
Wire, Violet, 16/0.2mm, 500m	MC16/0.2 TYPE 2 VIOLET 500M
Wire, Grey, 16/0.2mm, 500m	MC16/0.2 TYPE 2 GREY 500M
Wire, White, 16/0.2mm, 500m	MC16/0.2 TYPE 2 WHT 500M
Wire, Pink, 16/0.2mm, 500m	MC16/0.2 TYPE 2 PINK 500M
Wire, Red/Black, 16/0.2mm, 100m	MC6A-16/0.2T2-RDBK-100
Wire, Red/Brown, 16/0.2mm, 100m	MC6A-16/0.2T2-RD/BN-100
Wire, Red/Green, 16/0.2mm, 100m	MC6A-16/0.2T2-RDGN-100
Wire, Red/Blue, 16/0.2mm, 100m	MC6A-16/0.2T2-RDBE-100
Wire, Orange/Black, 16/0.2mm, 100m	MC6A-16/0.2T2-OEBK-100
Wire, Orange/Red, 16/0.2mm, 100m	MC6A-16/0.2T2-OERD-100
Wire, Yellow/Black, 16/0.2mm, 100m	MC6A-16/0.2T2-YWBK-100
Wire, Yellow/Red, 16/0.2mm, 100m	MC6A-16/0.2T2-YWRD-100
Wire, Yellow/Green, 16/0.2mm, 100m	MC6A-16/0.2T2-YWGN-100

Part Number Table

Description	Part Number
Wire, Green/Red, 16/0.2mm, 100m	MC6A-16/0.2T2-GNRD-100
Wire, Violet/Red, 16/0.2mm, 100m	MC6A-16/0.2T2-VTRD-100
Wire, Grey/Black, 16/0.2mm, 100m	MC6A-16/0.2T2-GYBK-100
Wire, Grey/Blue, 16/0.2mm, 100m	MC6A-16/0.2T2-GYBE-100
Wire, White/Black, 16/0.2mm, 100m	MC6A-16/0.2T2-WEBK-100
Wire, White/Red, 16/0.2mm, 100m	MC6A-16/0.2T2-WERD-100
Wire, Pink/Black, 16/0.2mm, 100m	MC6A-16/0.2T2-PKBK-100
Wire, Green/Yellow, 16/0.2mm, 100m	MC6A-16/0.2T2-GNYW-100
Wire, Purple/Red, 16/0.2mm, 100m	16/0.20 PUR/RED 100M
Wire, Green/Yellow, 16/0.2mm, 500m	16/0.20 GRN/YELL 500M
Wire, Black, 16/0.2mm, 100m	MC6A-16/0.2T3-BK-100
Wire, Brown, 16/0.2mm, 100m	MC6A-16/0.2T3-BN-100
Wire, Red, 16/0.2mm, 100m	MC6A-16/0.2T3-RD-100
Wire, Orange, 16/0.2mm, 100m	MC6A-16/0.2T3-OE-100
Wire, Yellow, 16/0.2mm, 100m	MC6A-16/0.2T3-YW-100
Wire, Green, 16/0.2mm, 100m	MC6A-16/0.2T3-GN-100
Wire, Blue, 16/0.2mm, 100m	MC6A-16/0.2T3-BE-100
Wire, Violet, 16/0.2mm, 100m	MC6A-16/0.2T3-VT-100
Wire, Grey, 16/0.2mm, 100m	MC6A-16/0.2T3-GY-100
Wire, White, 16/0.2mm, 100m	MC6A-16/0.2T3-WE-100
Wire, Pink, 16/0.2mm, 100m	MC6A-16/0.2T3-PK-100
Wire, Green/Yellow, 16/0.2mm, 100m	MC6A-16/0.2T3-GNYW-100
Wire, 100m, 0.75mm ² , Tc, Black	MC6A-24/0.2T2-BK-100
Wire, Brown, 24/0.2mm, 100m	MC6A-24/0.2T2-BM-100
Wire, 100m, 0.75mm ² , Tc, Red	MC6A-24/0.2T2-RD-100
Wire, Orange, 24/0.2mm, 100m	MC6A-24/0.2T2-OE-100
Wire, Yellow, 24/0.2mm, 100m	MC6A-24/0.2T2-YW-100
Wire, Green, 24/0.2mm, 100m	MC6A-24/0.2T2-GN-100
Wire, Blue, 24/0.2mm, 100m	MC6A-24/0.2T2-BE-100
Wire, White, 24/0.2mm, 100m	MC6A-24/0.2T2-WE-100
Wire, Pink, 24/0.2mm, 100m	MC6A-24/0.2T2-PK-100
Wire, Green/Yellow, 24/0.2mm, 100m	MC6A-24/0.2T2-GNYW-100
Wire, Yellow/Green, 24/0.2mm, 100m	24/0.20 YELL/GRN
Wire, Black, 24/0.2mm, 500m	MC6A-24/0.2T2-BK-500

Part Number Table

Description	Part Number
Wire, Red, 24/0.2mm, 500m	MC6A-24/0.2T2-RD-500
Wire, 24/0.2 Orange 500m	MC6A-24/0.2T2-OE-500
Wire, Blue, 24/0.2mm, 500m	MC6A-24/0.2T2-BE-500
Wire, Grey, 24/0.2mm, 500m	MC6A-24/0.2T2-GY-500
Wire, White, 24/0.2mm, 500m	MC6A-24/0.2T2-WE-500
Wire, Pink, 24/0.2mm, 500m	24/0.20 PINK 500M
Wire, Violet, 24/0.2mm, 500m	24/0.20 VIOLET 500M
Wire, Black, 24/0.2mm, 100m	MC6A-24/0.2T3-BK-100
Wire, Brown, 24/0.2mm, 100m	MC6A-24/0.2T3-BN-100
Wire, Red, 24/0.2mm, 100m	MC6A-24/0.2T3-RD-100
Wire, Orange, 24/0.2mm, 100m	MC6A-24/0.2T3-OE-100
Wire, Yellow, 24/0.2mm, 100m	MC6A-24/0.2T3-YW-100
Wire, Green, 24/0.2mm, 100m	MC6A-24/0.2T3-GN-100
Wire, Blue, 24/0.2mm, 100m	MC6A-24/0.2T3-BE-100
Wire, Violet, 24/0.2mm, 100m	MC6A-24/0.2T3-VT-100
Wire, Grey, 24/0.2mm, 100m	MC6A-24/0.2T3-GY-100
Wire, White, 24/0.2mm, 100m	MC6A-24/0.2T3-WE-100
Wire, Pink, 24/0.2mm, 100m	MC6A-24/0.2T3-YW-100F
Wire, Green/Yellow, 24/0.2mm, 100m	MC6A-24/0.2T3-GNYW-100
Wire, Black, 24/0.2mm, 500m	MC6A-24/0.2T3-BK-500
Wire, Red, 24/0.2mm, 500m	MC6A-24/0.2T3-RD-500
Wire, 24/0.2 Yellow 500m	MC6A-24/0.2T3-YW-500
Wire, White, 24/0.2mm, 500m	MC6A-24/0.2T3-WE-500
Wire, Black, 32/0.2mm, 100m	MC6A-32/0.2T3-BK-100M
Wire, Brown, 32/0.2mm, 100m	MC6A-32/0.2T3-BN-100
Wire, Red, 32/0.2mm, 100m	MC6A-32/0.2T3-RD-100
Wire, Orange, 32/0.2mm, 100m	MC6A-32/0.2T3-OE-100
Wire, Yellow, 32/0.2mm, 100m	MC6A-32/0.2T3-YW-100
Wire, Green, 32/0.2mm, 100m	MC6A-32/0.2T3-GN-100
Wire, Blue, 32/0.2mm, 100m	MC6A-32/0.2T3-BE-100
Wire, Violet, 32/0.2mm, 100m	MC6A-32/0.2T3-VT-100
Wire, Grey, 32/0.2mm, 100m	MC6A-32/0.2T3-GY-100
Wire, White, 32/0.2mm, 100m	MC6A-32/0.2T3-WE-100
Wire, Pink, 32/0.2mm, 100m	MC6A-32/0.2T3-PK-100
Wire, Green/Yellow, 32/0.2mm, 100m	MC6A-32/0.2T3-GNYW-100

Part Number Table

Description	Part Number
Wire, Yellow/Green, 32/0.2mm, 100m	32/0.20 YELLOW/GREEN
Wire, Black, 32/0.2mm, 500m	MC6A-32/0.2T3-BK-500
Wire, Red, 32/0.2mm, 500m	MC6A-32/0.2T3-RD-500
Wire, 32/0.2 White 500m ((Ns))	MC6A-32/0.2T3-WE-500
Wire, Blue, 32/0.2mm, 500m	32/0.20 BLUE 500M
Wire, Brown, 32/0.2mm, 500m	32/0.20 BROWN 500M
Wire, Pink, 32/0.2mm, 500m	32/0.20 PINK 500M
Wire, Yellow, 32/0.2mm, 500m	32/0.20 YELLOW 500M
Wire, Yellow/Green, 32/0.2mm, 500m	MC6A-32/0.2T3-GNYW-500
Wire, Black, 63/0.2mm, 100m	MC6A-63/0.2T3-BK-100
Wire, Red, 63/0.2mm, 100m	MC6A-63/0.2T3-RD-100

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.