


Daten & Signal, Socket, 3.5 mm, 3-pole, solder terminal, shielded



Description

- Solder terminal:
Screw-on mounting, from rear-side
- Data and Signal transfer
- Data and Signal Connectors 3-pole, shielded, straight
- Reinforced gold plating for increased insertions

References

Alternative: Housing insulated [4802.2310](#)


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)


Technical Data

Diameter	3.5 mm	Allowable Operation Temp.	-20 °C to 70 °C
Number of Poles	3-pole	Terminal	solder terminal
Ratings DC	1 A / 12 VDC	Mounting	Screw-on mounting wall thickness max. 2.0 mm
Ratings AC	1 A / 12 VAC	Housing	screened
Dielectric Strength	500 VDC	Style	straight
Insulation Resistance	> 10000 MΩ @ 500 VDC	Lifetime	10000 Insertions

Dimensions



Diagrams



Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Data and Signal Plug/Sockets	3.5	3-pole	solder terminal	4802.2300

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

Mating Inlets/Plugs

Category / Description



[Data and Signal Plug/Socket Overview complete](#)

Data & Signal, Plug, 3.5 mm, 3-pole, solder terminal, shielded 4802.1300

Data & Signal, Plug, 3.5 mm, 3-pole, solder terminal, insulated 4802.1310

[Data and Signal Plug/Socket further types to 4802 UK-Stecker, D=3,5mm](#)