



10" Polypropylene Woofer

MCM Part #: 55-1215 | MCM Audio Select Part #: 55-1215



10" Polypropylene Cone Woofer

Offering very good power handling and low frequency response, this woofer is ideal in traditional style three way enclosures, or as a subwoofer

Product Description

- Polypropylene cone
- Rubber surround
- Stamped steel basket
- Bumped and vented magnet
- 1.5" voice coil
- 26oz. magnet

Specifications::

- Power Capacity: 85W/150W RMS/peak
- Sensitivity: 94dB (W/M)
- Impedance: 8ohm
- Re: 6.8ohm
- Le: 0.83mH
- Frequency response: 30Hz~4KHz
- Fs: 30Hz
- Qts: 0.53
- Qes: 0.70
- Qms: 2.17
- Vas: 90.05 (liters)

- Xmax: 1.00mm

Dimensions:

- Overall frame diameter: 10.08"
 - Required cutout: 9.17"
 - Mounting depth: 4.92"
-