



8" (203 mm) High-Leverage Diagonal-Cutting Pliers - Angled Head

Cat. No. D248-8

Product Features

- *Angled head design for easy work in confined spaces.*
- *High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.*
- *Short jaws and beveled cutting edges permit close cutting of wire.*
- *Induction-hardened cutting knives for long life.*
- *Hot-riveted joint ensures smooth action and no handle wobble.*
- *Plastic-dipped handles for comfort and ease of identification.*
- *Custom, US-made tool steel.*



Handle Color: red

Cutting Knives: standard

Jaw Width: 1-3/16" (30 mm)

Jaw Thickness: 7/16" (11 mm)

Handle Finish: plastic-dipped

Jaw Length: 13/16" (21 mm)

Overall Length: 8-1/16" (205 mm)

Weight (lbs.): .60