



# 4" Shielded Aluminum Cone Woofer

MCM Part #: 55-1853 | MCM Audio Select Part #: 55-1853



4" Shielded Aluminum Cone Woofer  
**Versatile driver offers wide frequency response making it ideal in applications including full range, mid range, and midbass, in compact studio monitors, center channel speakers and multi driver arrays.**

## Product Description

---

- Aluminum cone
- Synthetic dust cap
- Rubber surround
- Fully shielded magnet structure
- Stamped steel basket
- 1" copper voice coil
- 8.6oz. magnet

### Specifications::

- Power Capacity: 20W/40W RMS/peak
- Sensitivity: 86dB (W/M)
- Impedance: 8ohm
- Re: 6.8ohm
- Le: 0.78mH
- Frequency response: 50Hz ~ 17KHz
- Fs: 60.0Hz
- Qts: 0.38
- Qes: 0.46

- Qms: 2.41
- Vas: 5.00 (liters)
- Xmax: 2.75mm

**Dimensions:**

- Overall frame diameter: 4.13" (pincushion)
- Required cutout: 3.66"
- Mounting depth: 2.80"