



Tenma 72-10405

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	40mV/400mV/4V/40V/400V/1000V	±(0.5%+1)
AC Voltage	40mV/400mV/4V/40V/400V/750V	±(1%+3)
DC Current	400μA/4000μA/40mA/400mA/4A/10A	±(1%+2)
AC Current	400μA/4000μA/40mA/400mA/4A/10A	±(1.2%+5)
Resistance	400 Ω /4kΩ/40kΩ/400kΩ/4MΩ/40MΩ	±(1%+2)
Capacitance	40nF/400nF/4μF/40μF/400μF/4000μF	±(3%+5)
Frequency	10Hz-10MHz	±(0.1%+4)
Temperature(°C)	-40°C~1000°C	±(1.2%+3)
Temperature(°F)	-40°F~1832°F	±(1.2%+4)
Special Functions		
Display Count		4000
Auto Range		√
Bandwidth (Hz)	45Hz-400Hz	√
Duty Cycle	0.1%~99.9%	√
Diode		√
Auto Power Off	Around 15 Minutes	√
Continuity Buzzer		√
Low Battery Indication	≅ 7.5V	√
Data Hold		√
Relative Mode		√
Max/Min		√
RS-232		√
LCD Backlight		√
Analogue Bar Graph	41	√
Input Protection		√
Input Impedance for DCV	Around :10MΩ	√
GENERAL CHARACTERISTICS		
Power	9V Battery (6F22)	
LCD Size	65 x 43mm	
Product Colour	Orange and Grey	
Product Net Weight	370g	
Product Size	180 x 87 x 47mm	
Standard Accessories	Battery, Test Lead, Multi-Purpose Socket, RS-232 Interface Cable, PC Software CD, Point Contact	
Standard Individual Packing	Gift Box , English Manual	
Standard Quantity Per Carton	20pcs	
Standard Carton Measurement	465 x 335 x 345mm	
Standard Carton Gross Weight	12kg	