



Tenma 72-10420

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	200mV/2000mV/20V/200V/500V	±(0.5%+2)
AC Voltage	200V/500V	±(1.2%+10)
DC Current	2000μA/20mA/200mA/10A	±(1%+2)
Resistance	200Ω/2kΩ/20kΩ/200kΩ/20MΩ	±(0.8%+2)
Temperature(°C)	-40°C~1000°C	±(1%+3)
Temperature(°F)	-40°F~1832°F	±(1%+4)
Special Functions		
Display Count		1999
Manual Range		√
Diode		√
Continuity Buzzer		√
Low Battery Indication		√
Data Hold		√
LCD Backlight		√
Input Impedance for DCV	Around :10MΩ	√

GENERAL CHARACTERISTICS

Power	9V Battery (6F22)	
LCD Size	48 x 16mm	
Product Colour	Orange and Grey	
Product Net Weight	179g(including holster)	
Product Size	130 x 73.5 x 35mm	
Standard Accessories	Probe	
Standard Individual Packing	Gift Box , English Manual	
Standard Quantity Per Carton	60pcs	
Standard Carton Measurement	490 x 356 x 315mm(0.055 CBM Per Standard Carton)	
Standard Carton Gross Weight	20kg	