


Number of contacts

8



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
<p>Crimp terminal</p> <p>Order crimp contacts separately</p>	<b>09 14 008 3001</b>	<b>09 14 008 3101</b>	<p>M</p> <p>F</p> <p>M</p> <p>F</p> <p>Contact arrangement view from termination side</p>	

Han Modular

Identification	Wire gauge (mm²)	Part number		Drawing	Dimensions in mm
		Male contact	Female contact		
<p>Crimp contacts</p> <p>Power contacts</p>				<p>Operating contact Identification</p> <p>Relay contact</p>	
<p>silver plated</p>	0.14-0.37	09 33 000 6127	09 33 000 6227		
	0.5	<b>09 33 000 6121</b>	<b>09 33 000 6220</b>		
	0.75	<b>09 33 000 6114</b>	<b>09 33 000 6214</b>		
	1	<b>09 33 000 6105</b>	<b>09 33 000 6205</b>		
	1.5	<b>09 33 000 6104</b>	<b>09 33 000 6204</b>		
	2.5	<b>09 33 000 6102</b>	<b>09 33 000 6202</b>		
	3	09 33 000 6106	09 33 000 6206		
	4	<b>09 33 000 6107</b>	<b>09 33 000 6207</b>		
<p>gold plated</p>	0.14-0.37	09 33 000 6117	09 33 000 6217		
	0.5	<b>09 33 000 6122</b>	<b>09 33 000 6222</b>		
	0.75	<b>09 33 000 6115</b>	<b>09 33 000 6215</b>		
	1	<b>09 33 000 6118</b>	<b>09 33 000 6218</b>		
	1.5	<b>09 33 000 6116</b>	<b>09 33 000 6216</b>		
	2.5	<b>09 33 000 6123</b>	<b>09 33 000 6223</b>		
	4	09 33 000 6119	09 33 000 6221		
<p>Relay contact silver plated</p>	0.75-1	09 33 000 6109			
	1.5	09 33 000 6110			
	2.5	09 33 000 6111			

Identification	Wire gauge	Stripping length
no groove	0.14-0.37 mm²	AWG 26-22
no groove	0.5 mm²	AWG 20
1 groove*	0.75 mm²	AWG 18
1 groove	1 mm²	AWG 18
2 grooves	1.5 mm²	AWG 16
3 grooves	2.5 mm²	AWG 14
wide groove	3 mm²	AWG 12
no groove	4 mm²	AWG 12

\* on the back crimp collar

Crimp contacts 0.14 ... 0.37 mm² only used with BUCHANAN crimping tool 09 99 000 0001

Stock items in bold type