



Female connectors, angled

| Identification  | No. of contacts | Contact length [mm] termination side | Part number                             |
|---|-----------------|--------------------------------------|---|
| Type AB <sub>19</sub>   | 95              | 3.4                                  | 17 33 095 1101<br><b>17 33 095 2101</b> |
| Type AB <sub>19</sub> with upper shield<br>CompactPCI, Position RJ3       | 95              | 3.4                                  | 17 33 095 1102<br><b>17 33 095 2102</b> |
| Lower shield for type AB <sub>19</sub> connectors                         |                 |                                      | 17 33 000 4102                          |
| Type AB <sub>22</sub>   | 110             | 3.4                                  | 17 34 110 1101<br><b>17 34 110 2101</b> |
| Type AB <sub>22</sub> with upper shield<br>CompactPCI, Positions RJ2, RJ5 | 110             | 3.4                                  | 17 34 110 1102<br><b>17 34 110 2102</b> |
| Lower shield for type AB <sub>22</sub> connectors                         |                 |                                      | 17 34 000 4102                          |
| Type AB <sub>25</sub>   | 125             | 3.4                                  | 17 35 125 1101<br><b>17 35 125 2101</b> |
| Type AB <sub>25</sub> with upper shield                                   | 125             | 3.4                                  | 17 35 125 1102<br><b>17 35 125 2102</b> |
| Lower shield for type AB <sub>25</sub> connectors                         |                 |                                      | 17 21 000 4102                          |

| Contact positions | X <sub>1</sub> | X <sub>2</sub> |
|-------------------|----------------|----------------|
| 19                | 37.9           | 18 x 2 (= 36)  |
| 22                | 43.9           | 21 x 2 (= 42)  |
| 25                | 49.9           | 24 x 2 (= 48)  |

Dimensions [mm]

