

## Item # 10069, Hour Meters (ETIs)

### Hour Meters (ETIs)



Model 635G Non-Resettable Round  
Round Style "G" measures ø2.687"

Time registration includes tenths increments i.e.: Hours/Tenths, Minutes/Tenths and Seconds/Tenths.  
Image shown in HOURS.  
Product shows MINUTES increments.

[SPECIFICATIONS](#) · [ELECTRICAL RATINGS AVAILABLE](#)

### SPECIFICATIONS

|                            |               |
|----------------------------|---------------|
| Model                      | 635 G         |
| Time Increments            | MIN           |
| Resettable                 | -             |
| Non-Resettable             | Y             |
| Reset Type                 | -             |
| Bezel Shape                | Round Style G |
| Bezel Size                 | ø2.687"       |
| Body Depth                 | 2.5"          |
| Body Diameter              | ø2.20"        |
| Mounting Style             | 3 Screw Panel |
| Operating Temperature Low  | -4 °F         |
| Operating Temperature High | 131 °F        |
| Approvals                  | UL/cUL        |

ELECTRICAL RATINGS AVAILABLE

|              |           |
|--------------|-----------|
| Voltage      | 115 V     |
| Frequency    | 60 Hz     |
| Current Type | AC        |
| Power        | 2.7 Watts |

---