



GE
Lighting



LED Decor Candle Dimmable

@LED4D/B35/827/230-
240V/B15/F/HBX1/6

97307

Product information

Where a decorative effect is needed, a 1W LED lamp can now be used where previously a 20W traditional halogen lamp was the lowest energy option. Just think about how much you can save! In addition do not forget that GE's LED Décor lamps also last up to 6 times longer compared to halogen lamps. Providing you with long-term reliability and hassle free decorative lighting.

Product data

Cap/Base	B15d
Bulb Shape	Candle
Bulb Finish	Diffuse
Bulb Diameter [mm]	36
Maximum Overall Length [mm]	102.5
Net weight per piece [g]	65
Gross weight per piece [g]	101
Regulatory comment	Remaining inventory is being sold out
Brand	General Electric (GE)

Performance data

Colour Rendering Index (CRI) [Ra]	80
Nominal correlated colour temperature (CCT) [K]	2700
Nominal lumens [lm]	220
Energy efficiency class (EEC)	A+
Rated life L70/B50 [h]	15000
Nominal power [W]	4
Nominal lamp voltage [V]	230

Electrical data

Weighted energy consumption [kWh/1000h]	4
Dimming Capability	Yes

Logistic data

DUN Code	10043168973073
EAN Code	0043168973076
Pack Quantity	6
Inner pack type	HANGING BOX
Outer pack type	TRAY OUTER
Layer quantity	288 EUR, 384 UK
Layer quantity EUR	288
Layer quantity UK	384
Pallet quantity EUR (PC)	2016
Pallet quantity UK (PC)	2688
Outer case size	145 x 98 x 125 (mm)
Product status	Marked for phase-out

Application areas



Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Product family datasheet \(PDF\)](#)

[Photometry \(IES\)](#)

[LED Lighting Solutions - Catalogue \(EN\) \(PDF\)](#)

[GLS, Candle, Spherical, Decor Data sheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

Photometric Data

