



GE  
Lighting



Pygmy - Clear

TU 15P1FRIDG/CL/SES 240V GE BL 1/6

**93491**

---

## Product information

GE incandescent lamps trace their ancestry to the world's first practical electric bulb, invented by Thomas Alva Edison, founder of General Electric Company, in 1879.

Available in all shapes and sizes, they offer particular qualities of light to suit specific applications.

---



WORLDWIDE PARTNER

## Product data

Cap/Base	E14
Bulb Shape	Pygmy
Bulb Finish	Clear
Bulb Diameter [mm]	26
Nominal Length [mm]	55
Net weight per piece [g]	20
Gross weight per piece [g]	41
Brand	General Electric (GE)

## Performance data

Nominal correlated colour temperature (CCT) [K]	2310
Nominal lumens [lm]	90
Rated efficacy [lm/W]	5.66667
Energy efficiency class (EEC)	E
Rated Life [h]	1000
Nominal power [W]	15
Nominal lamp voltage [V]	240

## Electrical data

Weighted energy consumption [kWh/1000h]	15.08
Dimming Capability	Yes

## Logistic data

DUN Code	20043168934910
EAN Code	5994100073260
Pack Quantity	6
Layer quantity	276 EUR, 342 UK
Layer quantity EUR	276
Layer quantity UK	342
Pallet quantity EUR (PC)	2208
Pallet quantity UK (PC)	2736
Outer case size	153 x 133 x 126 (mm)
Product status	Available

## Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Incandescent Lamps Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)