

Caps to Holder FEU, FEU (Med), FAU, FAC



250 VAC · 4 W / 16 A (VDE) · 600 VAC/DC · 16 A (UL/



Standards

- IEC 60127-6
- UL 4248-1 / UL 512
- CSA 4248-1 / no. 39

Approvals

- VDE Certificate Number: 134125
- UL File Number: E39328

References

Mating Cap to [FAC](#); [FAU](#); [FEU](#); [FEU \(Med\)](#); [SWG](#)

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Fuse-Link	5 x 20 or 6.3 x 32 mm
Rated Voltage	250 VAC (VDE), 600 VAC/DC (UL/CSA)
Rated current	10 A (VDE), 16 A (UL/CSA)
Rated Power Acceptance IEC	4 W / 16 A @ Ta 23 °C
Degree of Protection	IP 40
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Cap	Thermoplastic, UL 94V-0
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	

Dimension

31.5 mm



Variants

Cap	Fuse-Link	Degree of Protection	Colour Cap	Order Number
Slot Knob	6.3 x 32mm	IP 40	black	0031.1661
Slot Knob	5 x 20mm	IP 40	black	0031.1663
Slot Knob	6.3 x 32mm	IP 40	grey	0031.1666

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging Unit

Plastic Bag (100 pcs.)