


KEMET Part Number: C052K470K2X5CA
(CK05BX470K)

Capacitor, ceramic, 47 pF, +/-10% Tol, 200V, BX, Lead Spacing=0.2"



Dimensions (in)		
Symbol	Dimension	Tolerance
L	0.19	+/-0.01
H	0.235	+/-0.01
T	0.09	+/-0.01
S	0.2	+/-0.015
LL	1.25	MIN
F	0.025	+0.004/-0.002
K	0.19	+/-0.01
G	0.045	MAX

Notes:

-Note A: Center line of the leads will be within 0.03 in [0.76 mm] of the center line of the body.

-Lead length shown is for parts supplied in bulk. See packaging specifications for lead lengths when not provided in bulk

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	47 pF
Lead Spacing:	0.2"
Voltage:	200V
Temperature Coefficient:	BX
Tolerance:	+/-10%
Body Type:	Radial Molded
Lead Type:	Standard Leads
Lead Form:	Hockey Stick
Termination Type:	Tin-Lead (SnPb)

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100