


Capacitor, ceramic, 0.1 uF, +/-10% Tol, 50V, X7R



Dimensions (in)		
Symbol	Dimension	Tolerance
D	0.12	MAX
L	0.17	MAX
LL	1	MIN

Notes:

-Lead length shown is for parts supplied in bulk. See packaging specifications for lead lengths when not provided in bulk

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.1 uF
Temperature Coefficient:	X7R
Voltage:	50V
Tolerance:	+/-10%
Body Type:	Axial Conformal
Lead Type:	Standard Leads
Termination Type:	Tin (Sn)

Packaging Specifications	
Package Kind:	T&R
Package Type:	Standard
Package Quantity:	5000