

Main

Commercial Status	Commercialised
Product or component type	Buck and Boost Transformer
Box number	3A
NEMA degree of protection	NEMA 3R
Insulation temperature	221 °F (105 °C)
Primary voltage	120 x 240 V
Rated power in VA	0.15 kVA
Secondary voltage	12/24 V
Temperature rise	55 °C

Ordering and shipping details

Category	16265 - BUCK & BOOST
Discount Schedule	PE2
GTIN	00785901876090
Nbr. of units in pkg.	1
Package weight(Lbs)	7.80
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative