

Main

Commercial Status	Commercialised
Product or component type	Reversing Drum Switch
NEMA degree of protection	NEMA 1
Motor power hp	2 hp 230 V DC 2 hp 115 V DC 7.5 hp 575 V AC 7.5 hp 460 V AC 5 hp 230 V AC 5 hp 200 V AC 5 hp 575 V AC 5 hp 460 V AC 3 hp 230 V AC 1.5 hp 115 V AC
[Ue] rated operational voltage	250 V DC 600 V AC
Poles description	3P

Complementary

Product certifications	CSA UL listed
Electrical connection	Screw-clamp terminals
Range of product	B

Ordering and shipping details

Category	21116 - 2601
Discount Schedule	CP1
GTIN	00785901555438
Nbr. of units in pkg.	1
Package weight(Lbs)	2.33
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------