

Main

Commercial Status	Commercialised
Product or component type	Industrial Control Transformer
Product certifications	CE CSA UL listed
NEMA degree of protection	Not rated (open device)
Insulation temperature	356 °F (180 °C)
Network number of phases	1 phase
Rated power in VA	1000 VA
Primary voltage	240 x 480 V 230 x 460 V 220 x 440 V
Secondary voltage	120 V 115 V 110 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Range of product	T

Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901904724
Nbr. of units in pkg.	1
Package weight(Lbs)	21.66
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 1227 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	10 years
--------	----------