

ARCA 403015

Order symbol: ARCA 403015
Product nbr: 8120006
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the long side

EAN: 6418074079176
EI. number:
 Finland: 3423051
 Denmark: 8212091045
 Sweden: 2500112
 Norway:



Sample photo

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		400	300	150	Ingress Protection (EN 60529): IP 66
inch:		15.7	11.8	5.9	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		PUR			Certificates:
Temperatures:					Fimko
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 4030		Mounting plate			
MPP ARCA 4030		Mounting plate perforated			
MPX ARCA 4030		Mounting plate			
DRS ARCA 403015		DIN rail frame set			
DRS ARCA 403021		DIN rail frame set			
IDS ARCA 4030		Inner door set			
PMK ARCA 30		Pole mounting kit			

