

ARCA 806030



Sample photo

Order symbol: ARCA 806030
Product nbr: 8120019
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the long side

EAN: 6418074079305
EI. number:
 Finland: 3423115
 Denmark: 8212091171
 Sweden: 2500122
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		800	600	300	Ingress Protection (EN 60529): IP 66
inch:		31.5	23.6	11.8	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Gasket material:		PUR			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 8060		Mounting plate			
MPX ARCA 8060		Mounting plate			
MPP ARCA 8060		Mounting plate perforated			
DRS ARCA 806025		DIN rail frame set			
DRS ARCA 806030		DIN rail frame set			
IDS ARCA 8060		Inner door set			
PMK ARCA 60		Pole mounting kit			
Certificates:		Fimko			

ARCA 800x600x300

ARCA 600x800x300

