

ARCA 304015



Sample photo

Order symbol: ARCA 304015
Product nbr: 8120022
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the short side

EAN: 6418074079336
EI. number:
 Finland: 3423119
 Denmark: 8212091207
 Sweden: 2500111
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		300	400	150	Ingress Protection (EN 60529): IP 66
inch:		11.8	15.7	5.9	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Gasket material:		PUR			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 4030		Mounting plate			
MPP ARCA 4030		Mounting plate perforated			
MPX ARCA 4030		Mounting plate			
DRS ARCA 304015		DIN rail frame set			
DRS ARCA 304021		DIN rail frame set			
PMK ARCA 40		Pole mounting kit			
Certificates:					
Fimko					

