

**ARCA 507030**



Sample photo

**Order symbol:** ARCA 507030  
**Product nbr:** 8120031  
**Description:** Cabinet, PC  
**Remarks:** Grey cover, 2-point locking, hinges on the short side

**EAN:** 6418074086006  
**EI. number:**  
 Finland: 3424062  
 Denmark: 8212095384  
 Sweden: 2500119  
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.  
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		500	700	300	Ingress Protection (EN 60529): IP 66
<b>inch:</b>		19.7	27.6	11.8	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			UV resistance: UL 508
<b>Cover colour:</b>		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>		PUR			<b>Certificates:</b>
<b>Temperatures:</b>					Fimko
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
<b>Accessories:</b>					
MPS ARCA 7050		Mounting plate			
MPP ARCA 7050		Mounting plate perforated			
MPX ARCA 7050		Mounting plate			
DRS ARCA 507030		DIN rail frame set			
PMK ARCA 70		Pole mounting kit			

ARCA 700x500x300  
 ARCA 500x700x300

