

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [78315-0001](#)
Status: **Active**
Overview: [DDR3 DIMM Sockets](#)
Description: 1.00mm Pitch Aerodynamic DDR3 DIMM Socket, Very Low Profile, Vertical, Press-Fit, with Pegs, Black Housing and Latches, 0.76µm Gold (Au) Plating, 1.85mm Compliant Pin Length, 2.40mm PCB Thickness, 240 Circuits, Lead-Free

Documents:

[3D Model](#) [Application Specification AS-78315-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-78315-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Memory Module Sockets
 Series [78315](#)
 Application Tooling Part Link [62201-8656](#)
 Application Tooling Part Link [62202-3800](#)
 Component Type Socket
 Electrical Model Yes
 JEDEC Outline SO-012
 Overview [DDR3 DIMM Sockets](#)
 Product Name DDR3 DIMM
 UPC 800756929507

Physical

Circuits (Loaded) 240
 Circuits (maximum) 240
 Color - Resin Black
 Durability (mating cycles max) 25
 Entry Angle Vertical
 Flammability 94V-0
 Keying to Mating Part Yes
 Material - Metal Copper Alloy
 Material - Plating Mating Gold over Nickel
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 7.501/g
 PC Tail Length 1.85mm
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 2.40mm
 Packaging Type Tray
 Pitch - Mating Interface 1.00mm
 Pitch - Termination Interface 1.00mm
 Plating min - Mating 0.762µm
 Plating min - Termination 0.381µm
 Temperature Range - Operating -55°C to +85°C
 Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 1A
 Voltage - Maximum 30V AC (RMS)/DC



image - Reference only

Series

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[78315Series](#)

Mates With

JEDEC Standard 1.27mm Modules

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
DDR3 DIMM Memory Module Installation Tool	0622018656
DDR3 DIMM Memory Module Extraction Tool	0622023800

Voltage Key

Center

Material Info

Reference - Drawing Numbers

Application Specification
Electrical Model Document
Product Specification
S-Parameter Model
Sales Drawing

AS-78315-001
EE-78315-002, EE-78315-003
PS-78315-001, RPS-78315-001, RPS-78315-003
SP-78315-002, SP-78315-003
SD-78315-001

This document was generated on 12/11/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION