

**W-Series, Accessories**  
**WQV 2.5/4****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

The versatile and extensive range of products - from 0.05 mm<sup>2</sup> to 300 mm<sup>2</sup> - means that you have diverse options for your applications at your disposal. Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

**General ordering data**

Type	WQV 2.5/4
Order No.	<a href="#">1053860000</a>
Version	W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 4
GTIN (EAN)	4008190049706
Qty.	50 pc(s).

## Data sheet

### W-Series, Accessories WQV 2.5/4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Length	19.3 mm	Width	7 mm
Height	18 mm	Net weight	3.06 g

### Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	For the terminals		

### Rated data

Rated current	32 A
---------------	------

### Material data

Material	PA 66	Colour	Yellow
UL 94 flammability rating	V-2		

### System specifications

Product family	W-Series, Accessories
----------------	-----------------------

### Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

### Approvals

ROHS	Conform
------	---------

### Downloads

DXF	<a href="#">14685_WQV_2.5-4_DXF.dxf</a>
<a href="#">3-D model</a>	